

10	33 01 241 010 0007	FO multimode, 50/125 μm	10000 $\pm$ 100
9	33 01 241 009 0007	FO multimode, 50/125 μm	9000 $\pm$ 90
8	33 01 241 008 0007	FO multimode, 50/125 μm	8000 $\pm$ 80
7	33 01 241 007 0007	FO multimode, 50/125 μm	7000 $\pm$ 70
6	33 01 241 006 0007	FO multimode, 50/125 μm	6000 $\pm$ 60
5	33 01 241 005 0007	FO multimode, 50/125 μm	5000 $\pm$ 50
4	33 01 241 004 0007	FO multimode, 50/125 μm	4000 $\pm$ 40
3	33 01 241 003 0007	FO multimode, 50/125 μm	3000 $\pm$ 30
2	33 01 241 002 0007	FO multimode, 50/125 μm	2000 $\pm$ 20
1	33 01 241 001 0007	FO multimode, 50/125 μm	1000 $\pm$ 15
Cont. No.	Part-No.	Type of cable	Dim. a[mm]

- Protection level: IP20
- Temperature range: -10°C ...+70°C

