

WCY87

WCY87

WCY87 : WEJTAP CONN YEL



ACTIVE

RoHS compatible

Assistant

Add to Favorites

Email Datasheet

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Price request

Specifications

Download document

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Conductor Size (Run - Diameter)	0.893 to 1.25		
Conductor size (Run - Max)	1033.5-36/1		
Conductor size (Run - Min)	954.0-36/1		
Conductor Size (Run - mm)	23 mm² to 32 mm²		
Conductor Size (Run)	1033.5		
	1033.5-36/1		
	954.0-36/1		
Conductor size (Tap - Max)	1000		
Conductor size (Tap - Min)	954		
Conductor Size (Tap)	1000		
	954.0-36/1		
	954		
Conductor Type (Run)	ACSR		
	AAC		
Wire Size	AWG		
Wire Size (Tap - Diameter - in)	0.856 to 1.25		
Wire Size (Tap - mm)	22 mm² to 32 mm²		
Wire Type (Tap)	ACSR		
	AAC		
	Copper		
Physical			
Color Code	Yellow		
Approvals / Certifications			
UL Listed	No		
CSA Certified	No		
Other Features			
Installation Tool	WTY		
Booster	WPBY Box 25		
UPC	78181087575		
Keyword	wejtap		