

IP65 Low Energy Round Bulkheads



- Tough polycarbonate bulkheads
- IP65 rated
- Screw-down, shatterproof, weather-proof and UV resistant diffusers - prismatic or opal
- Available in maintained or standard versions
- Rated for continual use
- Suitable for indoor or outdoor applications
- Supplied with 28W Double-D Energy Saving lamps and control gear
- Dimensions (DxDia): 81 x 286mm

450196.311057,387064

Description	Order Code	Price Each
Standard		
White Opal	129-8374	
White Prismatic	129-8375	
Black Opal	129-8376	
Black Prismatic	129-8377	
Maintained		
White Opal	129-8378	
White Prismatic	129-8381	
Black Opal	129-8382	
Black Prismatic	129-8383	