Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'F6LE10D-10DM10'**

**Your search criteria matched only one product, shown below**

## F6LE10D-10DM10

• Colour-specific keys mechanically and visually distinguish connections to prevent positive and negative unintentional insertion into unlike keyed or non-keyed ports and allows design flexibility and versatility for a more discrete network
• Factory terminated and 100% tested for insertion loss (all) and return loss (10Gig™ and SM). Assures high performance for increased up-time and lower cost of ownership
• Low smoke zero halogen meets IEC-60332 (LSZH) flame rating for standard compliant safety
• Singlemode endfaces UPC polished (55dB min. return loss) ensures a high quality endface for higher return loss to meet application requirements
• Every singlemode endface is 100% factory inspected in compliance with Telcordia GR-326-CORE, Issue 3 requirements to assure high performance
• Keyed LC 10Gig™ Patch Cords and Pigtails are tested per IEEE 802.3ae 10 GbE to support network transmission speeds up to 10Gb/s for link lengths up to 300 meters for OM3 at 850nm to assure high performance and reliability
• Test data supplied with each patch cord and pigtail establishes a performance reference to streamline maintenance and troubleshooting

Additional lengths and availability: Keyed LC patch cords and pigtails are available in 1m – 10m lengths in 1m increments, and 15m, 20m, and 30m lengths. For other lengths, contact Customer Service for actual lead times.
Additonal keyed colors include the following: G– Violet, H– Aqua, J– Rose, K– Slate, L– Brown, P– White, Q– Charcoal, R– Lavender, S– Peach, T– Steel Blue, V– Maroon and W– Mint.

| | |
|---|---|
| Part Number | F6LE10D-10DM10 |
| RoHS Compliancy Status | RoHS directive is not applicable |
| Note | Intended for use in fixed installations which are outside the scope of RoHS. |
| Part Description | LC (keyed D- yellow) to LC (keyed D - yellow) LSZH, multimode duplex patch cord, 1.6mm jacketed cable (one duplex keyed LC connector on each end)– 62.5/125?m. |
| Product Type | Keyed LSZH Patch Cords |
| Length (m) | 10 |
| Fiber Compatibility | 62.5/125um |
| Fiber Cable Size | 1.6mm |
| Fiber Cable Type | Jacketed |
| Connector 1 Type | LC Connector- Keyed D (Yellow) |
| Connector 2 Type | LC Connector- Keyed D (Yellow) |
| Flammability Rating | LSZH (Low Smoke Zero Halogen) |
| Key Type and Color | Keyed D- Yellow |
| Pricing Description | Keyed LC (D-Yellow) to Keyed LC (D-Yellow), 62.5um, Duplex, LSZH, 10M |
| Min. Order UOM | PC |
| Min. Order Qty. | 1 |
| BOM Qty. (# of Pkgs.) | 0 |
| Add to Favorite Product List | |

**Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.**


Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy