Search Results

Evaluate
- FAQ's
Design a Solution
- Part Drawings
- PDF-PD Raceway C
- DWG-PD Raceway C
How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'PDC6EI6'**

Your search criteria matched only one product, shown below

PDC6EI6

Pan-Way® Type PD Surface Raceway is a single channel raceway system to route, protect and conceal power, data, voice, or video cabling.

- UL & CSA rated 600V; meets UL5A and CSA C22.2 No. 62.1-03 standards
- Textured Finish
- Tamper resistant latch design
- Raceway Base and Cover are packaged together
- FT-4 Rated for Canada

For actual product color please refer to the Surface Raceway Color Chart located in selection guides.

Part Number	PDC6EI6
RoHS Compliancy Status	Compliant
Part Description	Type P Cover- Size 6
Product Type	Power Rated Raceway
Color	Electric Ivory
CSA Certified	Yes
UL Listed	Yes
Height (In.)	0.46
Length (ft.)	6
Length (In.)	72.00
Width (In.)	1.29
Adhesive Backed	No
CE Compliant	No
Channel Type	Single-Channel
Mounting	Snap On
Pricing Description	PD6 Power Rated Raceway Cover ONLY6ft.
Product Length	6'
Product Size	6
Min. Order UOM	FT
Min. Order Qty.	6
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy