

**FLEX
STACK**

HDWM-08-56-L-D-312-SM

HDWM-24-59-L-S-300-SM

DWM-06-54-G-D-360

DWM, HDWM SERIES


MICRO BOARD STACKER

Mates with:
SMS, SLM, RSM

Rot
Yes

IPG@samtec.com)

RAI
FILE NO. E111594



RAI
FILE NO. E111594

TYPE STRIP	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	STACKER HEIGHT	OTHER OPTION
------------	------------------	------------	----------------	------------	----------------	--------------

01
thru
50

Specify
LEAD
STYLE
from
chart

—L
= 10 μ"
(0.25 μm)
Gold contact,
Matte Tin
on tail

—G
= 10 μ"
(0.25 μm)
Gold on post,
Gold flash
on tail

—S
= Single
Row

—D
= Double
Row

—“XXX”
= Stacker
Height
Example:
—250 =
(6.35 mm)
.250"

—“XXX”
= Polarized
Position
(Specify position
of omitted pin)

—SM
= Surface Mount
(Requires HDWM.
02 thru 40
positions only.)

—A
= Alignment Pin
(Requires HDWM.
6 positions min
—D only.)
Metal or plastic at
Samtec discretion
(N/A with —LC)

—LC
= Locking Clip
(Requires HDWM.
5 positions min.
—D only)
(N/A with —A)
(Manual placement
required)

—P
= Pick & Place Pad
(Requires HDWM)

DWM
= Standard Board Spacer

HDWM
= High Temp Board Spacer

LEAD STYLE	OAL	
	THROUGH-HOLE	SURFACE MOUNT
-01	(11.43) .450	(8.38) .330
-51	(10.41) .410	—
-52	(10.80) .425	—
-53	(12.83) .505	(9.78) .385
-54	(14.10) .555	(11.05) .435
-55	(15.49) .610	(12.45) .490
-56	(15.88) .625	(12.83) .505
-57	(16.51) .650	(13.46) .530
-58	(17.91) .705	(14.86) .585
-59	(19.18) .755	(15.62) .615
-60	(20.96) .825	—
-61	(26.67) 1.050	—

This Series is non-standard,
non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

*All parts within this catalog are built to Samtec's specifications.
Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.*