THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART#	COLOR	DESCRIPTION	WEIGHT*
CJS688TGY	BLACK	8 POSITION, 8 WIRE SHIELDED MODULE WITH INTEGRAL SHIELD. WIRE CAP LABEL IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	3.314 LB/100 PCS (1503g/100 PCS)
CJS688TGRDY	RED		
CJS688TGBUY	BLUE		
CJS688TGGRY	GREEN		
CJS688TGVLY	VIOLET		
CJS688TGYLY	YELLOW		

*WEIGHT IS APPROXIMATE

NOTES:
1. WHITE WIRE CAP DESIGNATES CATEGORY 6 PERFORMANCE.
2. MATERIAL:
   MODULE HOUSING-ABS
   SHIELD-TIN PLATED OVER PHOS. BRONZE
   WIRE CAP/CLIP - ZINC AND PC
3. ALL TX6 PLUS, 8 POSITION, 8 WIRE JACK MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION MODULAR PLUGS WITHOUT DAMAGE.
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.
5. .187 × .010" GROUNDING TAB PROVIDED AS OPTIONAL CONDUCTIVE PATH FOR GROUNDING.





ACTUAL SIZE

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
5	2-16-17	ROJC	NAGL	TMBA	MODEL REVISION UPDATED REMOVED PREVIOUS REVISIONS FOR CLARITY.	02479-357

PART NUMBER: CJS688TG**Y

TITLE: TX6 PLUS SHIELDED JACK MODULE

CUSTOMER DRAWING

ITEM REVISION NAME: M02479NS/08

DATASET FILE NAME: M02479NS_DC357/08A

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]
.X ± .XXX ± .010 [.3]
.XX ± .03 [.8] ANGLES ±
THIRD ANGLE PROJECTION

MATERIAL: SEE NOTE 2

DRAWING NUMBER: 02479-357

DRAWN BY	DATE	CHK	SCALE	SIZE
AFW	3-11-06	CEF	FULL	A

SHT 1 OF 1

D10100DA/14