


PRODUCT SPECIFICATION

Brand	Kasp
Product Range	Premium brass padlocks
Catalogue number	120
Date	12/03/2012

Range Description Premium brass padlocks		 120 series  Long shackle 		
Features • Hardened steel shackle (30mm and above) – extra protection against hacksaw and cropping attacks • Double bolted locking mechanism (30mm and above) – extra strength to resist torsion and pull attacks • Solid brass body – added resistance to corrosion				
Derivatives • Long shackle – provides greater shackle clearance for versatility				
Item Number	Item Description	EAN No	Commodity code	Carton Qty
K12020	Brass padlock 20mm - boxed	5013969900057	83011000	12
K12020D	Brass padlock 20mm display packed	5013969900064	83011000	6

K12025	Brass padlock 25mm – boxed	5013969900071	83011000	12
K12025D	Brass padlock 25mm – display packed	5013969900095	83011000	6
K12025A1	Brass padlock 25mm KA20251– boxed	5013969900088	83011000	12
K12030	Brass padlock 30mm – boxed	5013969900101	83011000	12
K12030D	Brass padlock 30mm – display packed	5013969900125	83011000	6
K12030A1	Brass padlock 30mm KA20301 – boxed	5013959900118	83011000	12
K12040	Brass padlock 40mm – boxed	5013969900132	83011000	12
K12040D	Brass padlock 40mm – display packed	5013969900156	83011000	6
K12040A1	Brass padlock 40mm KA20401 – boxed	5013969900149	83011000	12
K12040L55D	Brass padlock 40mm with 55mm long shackle – display packed	5013969900170	83011000	6
K12040L55A1	Brass padlock 40mm with 55mm long shackle KA – boxed	5013969900163	83011000	6
K12050	Brass padlock 50mm – boxed	5013969900187	83011000	6
K12050D	Brass padlock 50mm – display packed	5013969900200	83011000	6
K12050A1	Brass padlock 50mm – boxed	5013969900194	83011000	6
K12060	Brass padlock 60mm – boxed	5013969900224	83011000	6
K12060D	Brass padlock 60mm – display packed	5013969900248	83011000	6
K12060A1	Brass padlock 60mm KA20601 – boxed	5013969900231	83011000	6

Technical product information	Body – Solid brass				
	Locking mechanism- Pin tumbler cylinder type				
	Security rating, key differs and Use environment:				
	Item	Security rating	Key differs	Pins	Use Environment
	K12020	2	23	3	Light outdoor use
	K12020D	2	23	3	Light outdoor use
	K12025	2	23	3	Light outdoor use
	K12025D	2	23	3	Light outdoor use
	K12025A1	2	23	3	Light outdoor use
	K12030	3	580	4	Light outdoor use
	K12030D	3	580	4	Light outdoor use
	K12030A1	3	580	4	Light outdoor use
	K12040	4	2000	5	Light outdoor use
	K12040D	4	2000	5	Light outdoor use
	K12040A1	4	2000	5	Light outdoor use
	K12040L55D	4	2000	5	Light outdoor use
	K12040L55A1	4	2000	5	Light outdoor use
	K12050	6	2000	5	Light outdoor use
	K12050D	6	2000	5	Light outdoor use
	K12050A1	6	2000	5	Light outdoor use
	K12060	8	2000	5	Light outdoor use
	K12060D	8	2000	5	Light outdoor use
	K12060A1	8	2000	5	Light outdoor use

Shackle Dimensions and materials:

Dimensions mm	Dia	Internal width	Internal height	Material
K12020	3	10	13	Steel
K12020D	3	10	13	Steel
K12025	3	12	15	Steel
K12025D	4	12	15	Steel
K12025A1	4	12	15	Steel
K12030	5	16	18	Hardened steel
K12030D	5	16	18	Hardened steel
K12030A1	5	16	18	Hardened steel
K12040	6	22	22	Hardened steel
K12040D	6	22	22	Hardened steel
K12040A1	6	22	22	Hardened steel
K12040L55D	6	21	55	Hardened steel
K12040L55A1	6	21	55	Hardened steel
K12050	8	28	30	Hardened steel
K12050D	8	28	30	Hardened steel
K12050A1	8	28	30	Hardened steel
K12060	9.5	34	36	Hardened steel
K12060D	9.5	34	36	Hardened steel
K12060A1	9.5	34	36	Hardened steel

Recommended applications- Luggage, cupboards, lockers, toolboxes, sheds etc.

Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years Damage caused through inappropriate use or attempted break in is not covered
Country of origin	China

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K12020	20	10	36	31	28	12	46	32
K12020D	20	10	36	31	70	16	115	40
K12025	25	10	45	46	28	14	46	47
K12025D	25	10	45	46	70	16	115	56
K12025A1	25	10	45	46	28	14	46	47
K12030	30	13	54	98	35	17	61	99
K12030D	30	13	54	98	70	17	115	108
K12030A1	30	13	54	98	35	17	61	99
K12040	40	15	63	160	47	21	72	165
K12040D	40	15	63	160	100	19	155	179
K12040A1	40	15	63	160	47	21	72	165
K12040L55D	40	15	96	175	100	21	155	194
K12040L55A1	40	15	96	175	46	19	110	182
K12050	50	17	79	271	55	20	85	278
K12050D	50	17	79	271	100	23	155	297
K12050A1	50	17	79	271	55	20	85	278
K12060	60	19	90	415	64	21	95	424
K12060D	60	19	90	415	110	24	160	440
K12060A1	60	19	90	415	64	21	95	424

	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
Item	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
K12020	62	80	45	399		
K12020D	80	175	45	284		
K12025	62	85	45	579		
K12025D	80	185	55	384		
K12025A1	62	85	45	579		
K12030	75	110	67	1221		
K12030D	80	190	55	697		
K12030A1	75	110	67	1221		
K12040	95	135	80	2037		

K12040D	105	255	60	1158		
K12040A1	95	135	80	2037		
K12040L55D	105	270	60	1249		
K12040L55A1	120	115	50	1120		
K12050	90	135	57	1654		
K12050D	105	260	65	1867		
K12050A1	90	135	57	1654		
K12060	100	145	65	2578		
K12060D	115	170	145	2737		
K12060A1	100	145	65	2578		

Packaging waste details

	Primary Packaging				Secondary packaging			
Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
K12020			1	Box			15	Box
K12020D	6	Blister	3	Backing card			44	Box
K12025			1	Box			15	Box
K12025D	7	Blister	3	Backing card			48	Box
K12025A1			1	Box			15	Box
K12030			1	Box			33	Box
K12030D	7	Blister	3	Backing card			49	Box
K12030A1			1	Box			33	Box
K12040			5	Box			57	Box
K12040D	14	Blister	5	Backing card			84	Box
K12040A1			5	Box			57	Box
K12040L55D	14	Blister	5	Backing card			85	Box
K12040L55A1			7	Box			28	Box
K12050			7	Box			28	Box
K12050D	17	Blister	7	Backing card			85	Box
K12050A1			7	Box			28	Box
K12060			9	Box			34	Box
K12060D	17	Blister	17	Backing card			97	Box
K12060A1			9	Box			34	Box