

Cable White print
E320444 AWM STYLE 2725 80°C 30V VW-1 28AWG/1P 24AWG/2C
--c AWM I/II A 80°C 30V FT1 USB CABLE

PE Bag Packing



1PC/PE Bag

PIN ASSIGNMENT

P1		P2
1	Red	1
2	White	2
3	Green	3
4	Black	4
Shell	Drain+Braid	Shell

WSW P/N	Jacket color	Length(mm)
AK672/2-1-BLACK	Black	1000±30
AK672/2-2-BLACK	Black	2000±50
AK672/2-3-BLACK	Black	3000±50
AK672/2-5-BLACK	Black	5000±50

Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm max.
3. Insulator resistance: 10Mohm min.
4. Dielectric test: DC 300V

NO.	NAME.	Q'TY	SPECIFICATION
⑦	PE Bag	1	Clear Print black "MADE IN CHINA"+ "1PC"
⑥	TIE	1	Black
⑤	Out Jacket	6g	Black PVC-45P
④	Out Jacket	6g	Black PVC-45P
③	Cable	1	Black USB2.0 UL2725 28#/1P+24#/2C+AEB OD:4.7mm
②	CONN	1	USB 2.0 B Male Shell:Nickel Pin:G/F Insulator color: White
①	CONN	1	USB 2.0 A Male Shell:Nickel Pin:G/F Insulator color:White

RoHS compliant
Unit: mm

Scale	Free
TOLERANCE	
DIM	TOL
Angle	TOL

Id.	Modification	Date	Name
①	Update the drawing	26.01.2016	Amy
⓪	Drawn	11.02.2014	Joanna

	Date	Name
Drawn	11.02.2014	Joanna
Approved	26.01.2016	Amy

ASSMANN wsw components

Customer-No.

ASSMANN WSW-No.
AK672/2-x-BLACK

Drawing-No.
ASS 7067 CA

rev01

Replace

Sheet