# Replacement Heads for Pipemaster



## PIPEMASTER

| Specification | Details |
|---|---|
| Voltage | 220/240V AC |
| Power | 120W (600W Inrush) |
| Warm up time (from cold) | Approx. 4 minutes |
| Head temperature | 520° C |
| Usage time* 15mm | 1st joint 20-30 secs<br>2nd joint 10 secs |
| Usage time* 22 mm | 1st joint 30-40 secs<br>2nd joint 10 secs |
| Head sizes available | 8,10,14,15,16,18,22<br>3/8",½ ",¾ " ID (for USA) |
| Fitted heads | 15mm |
| Construction | Polycarbonate moulded parts<br>Stainless steel element shafts<br>Nickel plated copper heads |
| Lead wire | 3 core cable 1.8m |
| Plug | Moulded plug available as an option |
| Stand | Included, flat packed |

*Times can vary depending on condition of pipe, fittings, ambient temperature, etc..