Product Details for GPDQR

No Image Available

GPDQR

Tyco Part Number: 1-1423155-1

Active

Control Relays

Not ELV or RoHS Compliant

Product Highlights:

- GP Series
- Power
- DC Actuating System
- Input Voltage = 125 VDC
- Contact Arrangement = 1 Form C, SPDT, 1 C/O

View all Features

Quick Links

Check Pricing & Availability
Search for Tooling
Product Feature Selector
Contact Us
About This Product

Documentation & Additional Information

Product Drawings:
- None Available

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

Additional Information:
- Product Line Information

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Product Type = Power
- Termination Type = 16 Flat Base Pins

Electrical Characteristics:
- Actuating System = DC
- Input Voltage (VDC) = 125
- Contact Rating = 10A Resistive @ 220 VAC/48 VDC

Body Related Features:
- Series = GP

Contact Related Features:
- Approved Standards = CSA Certified, UL Listed
- Option = Coil Energization Light, Internal Coil Supression Diode
- Approx. Dimensions (L x W x H) (mm [in]) = 45.00 x 45.00 x 109.00 [1.773 x 1.773 x 4.294]
- Mounting Options = Socket

Configuration Related Features:
- Contact Arrangement = 1 Form C, SPDT, 1 C/O

Industry Standards:
- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not relevant for lead free process

Conditions for Usage:
- Temperature Range (°C) = 0 – 60

Other:
- Brand = Agastat

© 2006 Tyco Electronics Corporation All Rights Reserved