




## Top Entry PCB Jack



| Dimensions       |               |               |               |              |
|------------------|---------------|---------------|---------------|--------------|
| No. of Positions | A             | B             | C             | D            |
| 4                | 13.97<br>.550 | 11.43<br>.450 | 7.62<br>.300  | 3.81<br>.150 |
| 6                | 15.75<br>.630 | 13.46<br>.530 | 10.16<br>.400 | 6.35<br>.250 |
| 8                | 17.84<br>.700 | 15.36<br>.605 | 11.80<br>.465 | 8.89<br>.350 |

## Materials

**Housing:** Standard Material Glass Filled Polyester UL 94V-0

Standard Color Black

**Contact:** 0.46mm (0.018") Diameter Alloy C5210. Gold Plating Over Nickel

**Gold Plating:** As Per Customer Request.

## Ordering Information

| Positions/<br>Contacts | Description    | W/ Flange | Flangeless |
|------------------------|----------------|-----------|------------|
| 4P2C                   | Vertical Mount | 303042V   | 303042VFL  |
| 4P4C                   | Vertical Mount | 303044V   | 303044VFL  |
| 6P2C                   | Vertical Mount | 303062V   | 303062VFL  |
| 6P4C                   | Vertical Mount | 303064V   | 303064VFL  |
| 6P6C                   | Vertical Mount | 303066V   | 303066VFL  |
| 8P8C                   | Vertical Mount | 303068V   | 303068VFL  |

Standard contact plating is 1 micro inches of gold. For other platings add dash number as follows:

-6 = 6 Micro inches  
-30 = 30 Micro inches  
-50 = 50 Micro inches