Back to Result

AM2-M

Add to BOM | Add to Favorites

Low Profile Cable Tie Mount – User Supplied Adhesive

Product Details | Related Documents

Std. Pallet Weight (lb)	1,296.0000
Std. Pallet Volume (cf)	46.263843
Std. Ctn. Volume (cf)	1.2851
Std. Ctn. Weight (lb)	36.0000
Std. Pkg. Qty.	1000
RoHS Compliancy Status	Compliant
Part Description	Low Profile Cable Tie Mount – User Supplied Adhesive
Product Type	Cable Tie Mounts - User Supplied Adhesive
Material	Nylon 6.6
Color	Natural
UL Recognized	E136577
Length (mm)	31.2
Length (In.)	1.23
Height (mm)	3.2
Width (mm)	31.2
Width (In.)	1.22
Height (In.)	0.13
CE Compliant	Yes
Flammability Rating	V-2
Pricing Description	Cable Tie Mount, User-supplied Adh., Low Profile
Type	Tie Mount - User Supplied Adhesive
Mounting Method	User Suppled Adhesive
Used With Cable Ties	M, I, S
Environment	Indoor
Style	Tie Mount - Low Profile
Min. Order Qty.	1,000.0000