

P.C.B LAYOUT





N= NUMBER OF CONTACTS



Material
Terminal body
(contact pin): Brass(CuZn) Tin plated
Insulator (housing): Thermoplastic (UL94V-0),Green

Electrical cULus/CSA/VDE

Voltage rating: 300VAC/300VAC/300VAC
Current rating: 20A/20A/20A
Wire range:
Solid wire(AWG):
Stranded wire(AWG):
Withstanding Voltage: 1.6KV/2.5KV/2.5KV
Operating temperature: -30°C to +105°C
Soldering temperature: 250°C±10°C/5 Sec
Safety Approval:

RoHS compliant

Unit: mm

① File No.: E349947

Scale	1:1						Date	Name	Customer-No.
TOLERANCE						Drawn	10.12.2009	Dean	
X.	±0.50					Approved	18.04.2016	Joanna	ASSMANN WSW-No. A-TB500-OQxxCV
X.X	±0.30								
X.XX	±0.10								Drawing-No. ASS 3861 CO rev02
DIM	TOL	②	Add UL	18.04.2016	Joanna				
X.°	±1°	①	Drawn	10.12.2009	Dean				Replace Sheet
Angle	TOL	Id.	Modification	Date	Name				

ASSMANN WSW components