





*TO BE MEASURED ON LONGEST SIDE ONLY WITH THE WIRE IN INTIMATE CONTACT WITH THE BOTTOM OF THE GLASS WEDGE.

JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
505	24.0	.130	1.0	12.56	5,000	C-2F

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		JKL COMPONENTS CORPORATION TITLE T-3 1/4 STANDARD GLASS WEDGE BASE						
			DRAWN BY		APPV'D BY DATE		SIZE	FSCM NO.	DRAWING NO.				
A			UPDATED TO CAD DRAWING		6/12/00		L. WENGSTROM	QC	6/12/00				
			RELEASED		8/31/98								
REV. NO.	DESCRIPTION/ECO NUMBER				APPV'D DATE		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE	RELEASED DATE	REVISION DATE	REV. NO.	SHEET
									NONE	8/31/98	6/12/00	A	1 OF 1