

# SERIES 1299 - SINGLE-POLE POWER TOOL SWITCHES

TO 6 (6) A 250 V AC

ROCKER SWITCHES

PUSHBUTTON SWITCHES

TOGGLE SWITCHES

SLIDE SWITCHES

ROTARY SWITCHES

FOOT SWITCHES

POWER TOOL SWITCHES

FACT AND KEY SWITCHES

SNAP-ACTION SWITCHES

MICRO-SIGNAL SWITCHES

SENSORS

## PRODUCT FEATURES

- ◆ Single-pole normally open contact with integrated potential-free linear potentiometer
- ◆ Powerful with up to 6 A at 100 000 mechanical switching cycles
- ◆ With lock

## ON REQUEST

- ◆ Other colors
- ◆ Other actuator forms
- ◆ Other connection variants
- ◆ As changeover switch
- ◆ Right / left rotation
- ◆ Without lock
- ◆ Higher rating

Mechanical life endurance

1E5

Contact distance

> 3 mm

Material

actuator  
housing  
connections

PA / PA glass fiber-reinforced  
PA glass fiber-reinforced  
chromated

Approval marks

/ /

Suitable for appliances of protection class II



single-pole

Actuator color / printing

6 (6) A 250 V AC 5E4

13 A 125 V AC

Connection type

Connection description

Contact material

Miscellaneous

Stock version

### Normally open contact (SPNO)

1299.0101




2 x M3  
4 x terminal connection

Ag

R = 220 kOhm



Basic type 1299



Socket terminal M3,  
terminal connection