

REV. 3

DCO 102710

COIL: @ 25°C

RESISTANCE	300 OHMS ± 10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	13.0 VDC
MUST RELEASE	7.0 VDC MAX, 2.3 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 50 g's 11 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 15 MS MAX.
OPERATE BOUNCE 5 MS MAX
RELEASE BOUNCE 5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: 10 AMPS 28 VDC
5 AMPS 115 VAC/400 Hz RESISTIVE
50,000 OPERATIONS

DR. RB 8/6/93 CK. TLG 8-17-01

CII Technologies™
advanced control electronic solutions

CUST. QPL
CUST. NO. M5757/23-004 REV.

"07" RELAY

B07D934BC2-0052

F-718 REV. 3