main menue

home
test & measurement
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
oscilloscope test probes
measuring leads
plugs
2 mm system
2 mm safety system
4 mm system
4 mm sliding sleeve system
4 mm safety system
sockets
sets
miscellaneous

Search

Search

company

corporate association
location maps
fairs and exhibitions
jobs

SLS 200

datasheet for SLS 200
article number: 932153101

View Full-Size Image

SKS Kontakttechnik GmbH

product description:	order number: 932 153-101
description:	Banana plug, touch-protected, with capability of further connection, with solder connection for cross-sections up to 2.5 mm², insulated by latching and sprung insulated sleeve which is only released by pressure on the side-mounted locking spring. 4 mm dia
typ:	SLS 200 rot/red
system:	4 mm sliding sleeve system
order number:	932 153-101
color versions:	
technical data	
pin dimensions	4 mm with laminated spring
type of contact:	spring loaded pin
type of termination:	screw
rated voltage:	DC 300 V
rated current:	30 A
contact resistance:	5 mOhm
material	
contact material:	copper beryllium
contact surface material:	nickel-plated
housing material:	PP
environmental conditions:	
temperature range:	-25 ºC to +80 ºC
inflammable class:	
housing:	94 V-2
drawing	



search

Search..

Messetermine

No events

© 2009 www.sks-kontakttechnik.eu
Joomla! is Free Software released under the GNU General Public License.