




Mega Part Numbers
13-111160 to 13-111166
High Performance Chip Breaker Routers
Sizes 0.8mm – 3.0mm
 Common Shank Dia 1/8" (3.175mm)

D	L
0.80	5.00
1.00	5.00
1.20	5.00
1.50	6.00
2.00	7.50
2.50	8.50
3.00	8.50

All dimensions are in mm



ROUTING DATA PARAMETER RECOMMENDATIONS FOR FR4				
Diameter mm	Spindle Speed Rpm	X-Y Table Feed M/min	Z-FEED RATED (M/min)	
			Without pre-drilling	With Drilling
0.80	70000	0.3 – 0.4	0.2	0.4
1.00	70000	0.4 – 0.6	0.2	0.4
1.20	58000	0.5 – 0.7	0.4	0.8
1.50	46000	0.6 – 0.8	0.5	1.0
2.00	35000	1.0 – 1.4	0.5	1.2
2.50	28000	1.0 – 1.4	0.5	1.4
3.00	23000	1.0 – 1.3	0.4	1.4
The tabulated parameters provide guidelines which act as starting points for optimising speeds and feeds at the user's end				

MEGA ELECTRONICS LTD.

Mega House, Grip Industrial Estate, Linton, Cambridge, England. CB21 4XN

Telephone: +44 (0) 1223 893900 Fax: +44 (0) 1223 893894 email: sales@megauk.com web: www.megauk.com