


JKL LAMP PART NUMBER	COLOR 5600°*k (REF.)	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mA rms)	BRIGHTNESS (CANDELA/m <sup>2</sup> )	*RATED LIFE (HRS)
BF26214-20B	x = 0.333 ± 0.01 y = 0.345 ± 0.01	1450 @ 0°C	620	5	30,000 ± 10%	20,000

\* RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

			<b>METRIC</b>		<b>JKL COMPONENTS CORPORATION</b>	
					TITLE	
			THIRD ANGLE PROJECTION		MINIATURE COLD CATHODE FLUORESCENT LAMP	
			DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWING NO.	
			1 PL +/- 0 2 PL +/- 0 ANGLE +/- 0		BF26214-20B	
C	STRAIGHT ENDS + x & y's	7/7/03	DRAWN BY	APPV'D BY DATE	SIZE	FSCM NO.
B	214±3.0 TO 214±2.0	5/18/01	L. WENGSTROM	F.D. 7/7/03	A	55335
A	DIMENSION CORRECTION-240 TO 214	12/19/00	- CAD DRAWING -		SCALE	RELEASED
	RELEASED	12/5/00	MANUAL REVISIONS NOT PERMITTED		NONE	DATE 12/5/00
REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE			REVISION DATE	REV. NO.
					7/7/03	C
						SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[BF26214-20B](#)