




General ordering data

Order No.	1565250000
Part designation	KLIPPON K02
Version	Housings, 34 mm, 64 mm, 98 mm, Aluminium alloy (AlSi12)
EAN	4008190085025
Qty.	6 pc(s).

Dimensions

Fixing dimension, width	86 mm
Height	34 mm
Length	64 mm
Width	98 mm

General details

Cover fixing	4 stainless steel M4 screws
Enclosure fixing	Holes 4 mm
Integral fixing	Threaded holes M3
Resistance to shocks	10 J
Sealing material	Neoprene
Version cover	closed
Surface finish	untreated
Class of protection to EN 60529	IP 66 and IP 67
Weight	200 g
Ambient temperature, min.	-30 °C
Ambient temperature, max.	80 °C

Screwed cable glands top/bottom

M 12	1
M 16	1
Side of enclosure	Top / Bottom

Screwed cable glands, left/right

M12	3
M16	3

Screwed cable glands, left/right

On housing side left / right

Approvals

Approvals institutes

**Classifications**

ETIM 2.0	EC000058
ETIM 3.0	EC000058
eClass 4.1	27-14-12-06
eClass 5.0	27-14-91-07
eClass 5.1	27-14-91-07

Similar products

Order No.	Part designation	Version
9529110000	KLIPPON K02 RAL7001	Housings, 34 mm, 64 mm, 98 mm, Aluminium alloy (AlSi12)