THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2013
© COPYRIGHT 2013 BY TE CONNECTIVITY. ALL RIGHTS RESERVED.

LOC	DIST
-	-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER E.O. P20076	9DEC2008	-	RDR
	E	REVISED PER E.O. P20790	4FEB2011	-	RDR
	F	REVISED PER E.O. P21394	6JUN2012	-	RDR
	F1	REVISED PER ECO-14-002953	29JAN2014	PV	DM





5. MATERIAL: RECEPTACLE HOUSING AND WELD RING: PA 15%GF (GREY)
GROMMET: SILICONE (RED)

4. OVERALL DIMENSION DOES NOT INCLUDE RUBBER GROMMET.

3. THIS RECEPTACLE MATES WITH FOLLOWING PLUG (X = SEAL TYPE, XXXX = ALL MODIFICATIONS).
HD16-3-96SX-XXXX

2. SEE DRAWING 0425-015-0000 FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS.

1. SEE TABLE FOR USABLE WIRE RANGE AND INSULATION RANGE.

CONTACT SIZE	MINIMUM O.D.	MAXIMUM O.D.	WIRE RANGE [mm^2] 2
16	.100 [2.54]	.150 [3.81]	14-20 AWG [2.0-.50]

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES[mm]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±
2 PLC ±
3 PLC ±.025
4 PLC ±
ANGLES ±0° 30′0″

MATERIAL 5

FINISH -

DWN J.HAYNES 2SEP1999
CHK I.GRANTCHAROVA 17SEP2013
APVD D.MEYER 19SEP2013
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT 15.68 (g)

TE Connectivity

NAME RECEPTACLE CONNECTOR
INLINE HD10 SERIES
ARR. 3-96 COLOR: GREY

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-HD14-3-96P	-

Customer Drawing

SCALE 2:1 SHEET 1 OF 1 REV F1

1470-19 (3/11)