



LOC		DIST		REV		DATE		APPRO	
G	14	P	F	ZONE	LTR	DESCRIPTION	DATE	APPRO	DATE
				D		REV. RDRW, 2 SM PKG PER 0720-0040-93	4-8-93	18 DAP	



AMP WIRE RANGE	UL E13288 Listed
16-14 AWG	16-14 AWG
SOLID OR STRANDED	SOLID OR STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
16-14 AWG	
SOLID OR STRANDED	NOT APPLICABLE

△ STAMP AMP 16-14* APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
1.04-2.62mm² (2,050-5,180) CIR MILS
SOLID OR STRANDED

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm (INCHES)
TOLERANCES ON:
2 PLC DEC ±
3 PLC DEC ±
ANGLES ±

FINISH
TIN PLATE
0.00254 (0.00100) MIN
THK PER MIL-T-10727

DR 4-8-93
TA BRINKMAN
CHK 4-8-93
DA PATTERSON
APPD 4-8-93
DE MILLER
APPD 4-8-93
JL MECKLEY
PRODUCT SPEC
APPLICATION SPEC
WEIGHT

QUANTITY	PACKAGING TYPE	PART NO
100	LOOSE PIECE, BOX	8-320856-1
5000	ON TAPE	2-320856-1
---	LOOSE PIECE	320856

TERMINAL, FLANGED
SPADE, SOLISTRAND™



AMP Incorporated
Harrisburg, PA 17105-3608

SIZE
CAGE CODE
DRAWING NO
SCALE 10:1
SHEET 1 OF 1