- Heatsinks f.cool
  - Profile heatsinks and fluid coolers
  - Heatsinks and active heatsinks for processors
  - Board Level heatsinks
  - Cooling aggregates
    - Segment cooling aggregates
    - Miniature cooling aggregates
    - Cooling aggregates with axial fan
    - High-performance heatsinks
    - Cooling aggregates with radial fan
    - Protection grid for fans
  - Accessories for electronic components
- Cases f.case
- Connectors f.con

Cooling aggregates with axial fan

LA V 14 ...

LA V 14 300 230

120 x 120 mm, with axial fan and air-flow chamber

Data sheet | add to request

Features | Technical Drawing | Fan | Service | Accessories / related products

width B	120 mm
height	120 mm
length	300 mm
thermal resistance R_{th}	0.11 - 0.05 K/W
surface	raw degreased aluminium mounting area(s) milled flat
operating voltage of the fan motor	24 V DC 230 V AC