PRODUCT CATEGORIES
- Air Hammers
- Alligator Clips
- Pins and Accessories
- Alligator Clips
- Pin Accessories
- Plug Accessories
- Flash Sales Items
- Sales Flyers
- Alligator Clips Sales Flyer
- Pin Accessories Sales Flyer
- Plug Accessories Sales Flyer
- Sales Flyers
- Alligator Clips Sales Flyer
- Pin Accessories Sales Flyer
- Plug Accessories Sales Flyer
- Quick Ordering
- Request Catalog
- Contact Us
- Home Page

ISO 9001:2000

Multi-Purpose Clips

Mueller Electric is the manufacturer of **alligator clips, test leads, and banana plugs**. While the founder of **Mueller Electric Company** started manufacturing the first alligator clips and test leads, the company has since made other test leads, test accessories, and board to board connectors, sold to qualifying customers and distributors. Mueller Electric has been known as a wide variety of battery clips and electrical connectors.

Heavy Duty Clip for Grounding Applications

Model # (Ex.) CHP6BS-1 / HP7BS-1 / CP6BS-1 / CP5

- Copper version has a tog connection
- Copper alloy (Ex.) CP5 or CP6
- Clip unplated (Ex.) CHP6BS or unplated and marked (Ex.) HP7BS
- Clip plated (Ex.) CP5
- Length 3" (76 mm)
- Packed Spec: CE AA3968-001 (Bu) / HCP6; Rating: 100 Amps / HCp; 200 Amps / PCC

Insulator for Heavy Duty Clip

Model # (Ex.) 5-1

- Protective flexible vinyl insulator for 1/4, 1/C
- Material: PVC
- Length 1" (25mm)
- Tail Colors: 4 Black, 2 Red, 4 Yellow, 3 Green, 4 Blue, 8 White

Heavy Duty Clip for Battery and Test Work

Model # (Ex.) CHP6BS-2 / HP7BS-2 / CP6BS-2 / CP5

- Crimp or screw connection, copper version (CC)
- Copper version has a tog connection (Ex.) CHP6BS-1 (8" (203 mm) Max. (Ex.) HP7BS-2 (8" (203 mm) Max.
- Copper alloy unplated (Ex.) CHP6BS or unplated and marked (Ex.) HP7BS
- Material: zinc plated steel (ZY) or solid copper (CC) Spring: steel
- Length 3" (76 mm) / 8" (203 mm)
- Packed Spec: CE AA3968-001 (Bu) CCPN
- Rating: 50 Amps (CY) or 100 Amps (CC)

Insulator for Heavy Duty Battery Test Clip

Model # (Ex.) 5-2

- Protective flexible vinyl insulator for 2/4, 2/C
- Material: PVC
- Length 3" (76mm)
- Tail Colors: 4 Black, 2 Red, 4 Yellow, 4 Green, 4 Blue, 8 White

Heavy Duty Clip

Model # (Ex.) CHP7BS(-)/HP7

- Crimp or screw connection, jaw opens 0.75" (19 mm) max. barb insert on three sides of the jaw
- Copper alloy unplated (Ex.) CHP7 or solid copper (Ex.) CC Spring: steel
- Length 3" (76 mm)
- Packed Spec: CE AA3968-000 (Bu) CBC
- Rating: 40 Amps (Ex.) CC / 75 Amps (Ex.) CBC

Automotive Clip

Model # (Ex.) CH-2/(Ex.) CC

- Crimp or screw connection, jaw opens 0.75" (19 mm) max. barb insert on three sides of the jaw
- Copper alloy unplated (Ex.) CH or solid copper (Ex.) CC Spring: steel
- Length 2" (51 mm)
- Packed Spec: CE AA3968-000 (Bu) CBC
- Rating: 40 Amps (Ex.) CH / 75 Amps (Ex.) CBC

Insulator for Automotive Clip

Model # (Ex.) 5-1

- Protective flexible vinyl insulator for 2/4, 2S, 2C
- Material: PVC
- Length 1/8" (56.5 mm)
- Tail Colors: 4 Black, 2 Red, 4 Yellow, 3 Green, 4 Blue, 8 White

General Purpose Clip

Model # (Ex.) CT-5/(Ex.) CC

- Crimp or screw connection
- Copper alloy unplated (Ex.) CT or solid copper (Ex.) CC Spring: steel
- Length 1" (25 mm)
- Packed Spec: CE AA3968-000 (Bu) CTC
- Rating: 20 Amps (Ex.) CT / 40 Amps (Ex.) CTC

Geophone Clip

Model # (Ex.) CTC/(Ex.) CTCW

- Crimp or screw connection, jaw opens 0.625" (16 mm) max curved jaws dig cut to accommodate rings
- Copper alloy unplated (Ex.) CTC Spring: steel
- Length 1.4" (37 mm)
- Rating: 40 Amps

General Purpose/Geophone Clips

Model # (Ex.)5-4

- Protective flexible vinyl insulator for 2T, 2TC, 2TCG, and 2TCGW
- Material: PVC
- Length 1.5" (38 mm)
- Tail Colors: 4 Black, 2 Red, 4 Yellow, 3 Green, 4 Blue, 8 White

Welding Clip

Model # (Ex.) CC

- Lug connection
- Jaw opens 1.81" (46 mm) max
- Copper alloy Spring: steel
- Length 1.75" (108 mm)
- Packed Spec: CE AA3968-012
- Rating: 300 Amps

Insulator for Welding Clip

Model # (Ex.) 5-7

- Protective flexible vinyl insulator for 3/C
- Material: PVC
- Length 3" (102mm)
- Tail Colors: 4 Black, 2 Red

Pos-Wire Clip

Model # (Ex.)CH-5

- Crimp or screw connection
- Jaw opens 0.31" (7.9 mm) max
- Material: zinc plated steel (ZY) or solid copper (CC) Spring: steel
- Length 1.54" (39.5mm)
- Packed Spec: CE AA3968-000 (Bu) HCC
- Rating: 5 Amps (Ex) HCc / 15 Amps (Ex) HCC

Insulator for Pos-Wire Clip

Model # (Ex.) 5-7

- Protective flexible vinyl insulator for 4S, 4SC
- Material: PVC
- Length 1" (25.2 mm)
- Tail Colors: 4 Black, 2 Red, 4 Yellow, 3 Green, 4 Blue, 8 White

Automotive Analyzer Clip

Model # (Ex.)4SB/(Ex.)4SC

- Screw or crimp connection
- Jaw opens 0.31" (7.9 mm) max
- Copper alloy unplated (Ex.) 4SB or solid copper (Ex.)4SC Spring: steel
- Length 1.54" (39.5mm)
- Packed Spec: CE AA3968-000 (Bu) 4SC
- Rating: 10 Amps (Ex) 4SB / 20 Amps (Ex) 4SC

Automotive Analyzer Clip

Model # (Ex.) 4SB/(Ex.) 4SC

- Screw or crimp connection
- Jaw opens 0.31" (7.9 mm) max
- Copper alloy Spring: steel
- Length 1" (25.4mm)
- Rating: 10 Amps

Insulator for Automotive Analyzer Clip

Model # (Ex.) 4S-7

- Protective flexible vinyl insulator for 4SB, 4SB2E, 4SC, 4SC2E, 5S, 6S
- Material: PVC
- Length 1.38" (35.0mm)
- Tail Colors: 4 Black, 2 Red, 4 Yellow, 3 Green, 4 Blue, 8 White

Meter Testing Clip With Needle

Model # (Ex.) 6-1

- Solid copper clip with beryllium copper piercing needle in the test pin
- Copper alloy unplated (Ex.) mm
- Material: Solid copper
- Length 1.38" (35" 10mm)
- Packed Spec: CE AA3968-012
- Rating: 20 Amps

Meter Testing Clip

Model # (Ex.)10

- Same as 6S SOC except without insulation piercing needle
- Material: Solid copper
- Jaw opens 0.31" (12.7 mm) max
- Length 1.38" (35mm)
- Length 2.28" (57 10mm)
- Rating: 20 Amps

Economy Clip

Model # (Ex.)8

- Screw or crimp connection
- Jaw opens 0.44" (11.1 mm) max
- Material: zinc plated steel
- Length 1.5" (38mm)
- Rating: 15 Amps

Grounding Clamp

Model # (Ex.)9

- Attaches to pipe up to 1.18" outer diameter
- Material: Solid copper
- Length 2.37" (60.75mm)
- Rating: 50 Amps

Insulator

Model # (Ex.) 7A-1

- Protective flexible vinyl insulator for 10
- Accepts 0.37" (7 mm) gripper wire
- Material: PVC
- Length 2.6" (67mm)
- Tail Colors: 4 Black, 2 Red, 4 Yellow, 3 Green, 4 Blue, 8 White

Insulator for General Purpose/Geophone Clips

Model # (Ex.)5B-1

- Protective flexible vinyl insulator for 2T, 2TC, 2TCG and 2TCGW
- Material: PVC
- Length 1.5" (38mm)
- Tail Colors: 4 Black, 2 Red, 4 Yellow, 3 Green, 4 Blue, 8 White