REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED

NOTES: UNLESS OTHERWISE SPECIFIED

1. CONSTRUCTION:
   INSULATOR: P.V.C. AVAILABLE IN BLACK OR RED.
   CONTACT: ANACONDA 7021 OR BOILCAT C97.
   GOLD PLATED.
   SOCKET: BRASS. TIN PLATED.

2. PERFORMANCE:
   MAXIMUM CURRENT: 15 AMPS
   MAXIMUM VOLTAGE: 300 V
   MAXIMUM TEMPERATURE: 122°F (50°C)



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS ± DECIMALS .XX ± .XXX ± ANGLES ±	CONTRACT NO.	E-Z-HOOK® DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.
			APPROVALS / DATE	
			DRAWN R.L. 3/09	DESCRIPTION
		MATERIAL SEE NOTE.	APPROVED BY	E-Z-FLEX BAN SKT TO 0.094 [2.39] PIN ADAPTER (12AWG)
		FINISH SEE NOTE.		SIZE A / CODE IDENT NO. 08505 / DRAWING NO. 9341 / REV.
NEXT ASSY	USED ON			
APPLICATION		DO NOT SCALE DRAWING		SCALE 2:1 / SHEET 1 OF 1

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-Z-HOOK. THE INFORMATION IS NOT TO BE REPRODUCED WITHOUT PRIOR WRITTEN PERMISSION OF E-Z-HOOK, DIV. OF TEKTEST INC.
MAXIMUM TESTED RATINGS IN A HANDS-FREE CONTROLLED ENVIRONMENT. MAXIMUM RATINGS ARE NOT TO BE USED CONCURRENTLY.