THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -.- .
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST
CM	00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	REVISED PER 0G3B-0888-03	29-JAN-04	SH	DC



1. HAND TOOL PART NUMBER 734202-3
2. EXTRACTION TOOL PART NUMBER 188688-1
3. LOOSE PIECE CONTACT
4. AMP TRADEMARK
5. MATERIAL PHOSPHOR BRONZE PRETINNED 1-3μm
6. CUT OFF DIMENSION FOR LOOSE PIECE CONTACT 0.5 [.02] MAXIMUM.
7. WIRE RANGE: 0.12-0.35mm^2 [.005-.014in^2], (22-26 AWG).
8. INSULATION RANGE: 1.20-1.75 [.050-.070] DIAMETER.





SECTION B-B
SCALE 14:1





SECTION A-A
SCALE 14:1

DIRECTION OFF TOP OF REEL



106528

METRIC

3 PRETINNED	PHOSPHOR BRONZE	1-106528-2
PRETINNED	PHOSPHOR BRONZE	106528-2
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ± 0.10 [.004]
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL: SEE CHART
FINISH: SEE CHART

DWN S. HOOVER 29-JAN-2004
CHK D. COLEY 29-JAN-2004
APVD D. COLEY 29-JAN-2004
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
CUSTOMER DRAWING

tyco Electronics
Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME: SOCKET CONTACT AMP-DUAC™

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-106528	—

SCALE 14:1 SHEET 1 OF 1 REV G

AMP 1471-9 REV 31MAR2000