










PACKAGED 190 PIECES IN A TRAY	8 POS. 8 CONT.	OVERALL: Ni 1.27 μm MIN. ALL OVER THE CONTACTS	HOUSING: PBT UL 94 V-0 BLACK	2-338556-1		
		SOLDER ZONE: Sn 2.5 μm MIN. ON THE SOLDER ZONE OF THE CONTACT	CONTACTS: PHOSPHOR BRONZE			
		MATING ZONE: PLATING CONFIRMS TO PRODUCT REQUIREMENTS AS PER SPECIFICATION 108-19064	SHIELD: BRASS PRE-PLATED (BRIGHT TIN)			
PACKAGING	REMARKS	DESCRIPTION	MATERIAL	P/N		
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.v.EIJK CHK M.v.ESSSEN APVD R.SMEETS	 TE Connectivity			
DIMENSIONS: mm		NAME 8 pos. Modular Jack Side Entry fully shielded with insulation plate				
		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.15 1 PLC ±0.15 2 PLC ±0.15 3 PLC ±0.15 4 PLC ±0.15 ANGLES #0°30'	-			
		PRODUCT SPEC 108-19064 APPLICATION SPEC 114-19019	-			
MATERIAL	FINISH	WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C=338556	RESTRICTED TO -
-	-	-	CUSTOMER DRAWING			
			SCALE 4:1	SHEET 1	OF 2	REV K

