THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

A

E

PANDUIT PART NUMBER	WEIGHT
FR6TRBE58 FR6TRBE58M	1.25 LB/EACH (567g/EACH)

F



D NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
2. THE FIBERRUNNER 4x4 AND 6x4 QUIKLOCK EXISTING THREADED ROD BRACKET IS USED TO SUPPORT THE FIBERRUNNER 4x4 AND/OR 6x4 CABLE ROUTING SYSTEMS FROM A SECTION OF EXISTING 5/8" (M16) THREADED ROD.
3. THE FIBERRUNNER 4x4 AND 6x4 QUIKLOCK EXISTING THREADED ROD BRACKET INCLUDES:
   ONE (1) BRACKET ASSEMBLY,
   TWO (2) 5/8-11 SPLIT LOCK NUTS (FR6TRBE58 ONLY),
   TWO (2) M16x2 SPLIT LOCK NUTS (FR6TRBE58M ONLY).
4. FINISH COLOR: BLACK (EXCEPT HARDWARE)
5. DIMENSIONS IN PARENTHESES ARE IN METRIC.







ENG. REF.: D37585CY_DC_FR6TRBE58_01.prt

CAD FILENAME/LAYERS C FR6TRBE58.pdf

PANDUIT CORP TINLEY PARK, ILLINOIS

FIBERRUNNER 4x4 AND 6x4 QUIKLOCK EXISTING THREADED ROD BRACKET - 5/8" (M16) THREADED ROD (FR6TRBE58, FR6TRBE58M) B G H

CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ±
(.XX) ±.03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JHNU
MAT'L: STEEL
SCALE NONE
DATE 11-3-00
CHK'D HIW
DRAWING NO. 37585-70
DWG A
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	GMBH
-	--------	---	--	H. REMOVED ALL REFERENCES TO FR6TRBE12M	--------	--	--			
-	--------	---	--	G. REVISED TO INCLUDE FR6TRBE58	--------	--	--			
-	--------	---	--	F. REVISED PART WEIGHT E. REVISED CHART	--------	--	--			
-	--------	---	--	D. REVISED GENERAL NOTES C. REVISED CAD FILENAME	--------	--	--			
1	8-1-06	MSO	RN	B. REVISED DRAWING TITLE A. REVISED AND REDRAWN	37585-70	RN	RN			