Search Results

Evaluate
- FAQ's
Design a Solution
- Specification Sheets
- PDF-Mini-Com Min..
How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor
Install & Maintain
- Installation Instructions
- PDF-Mini-Com Min..

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'CJ588ORY'**

Your search criteria matched only one product, shown below

CJ588ORY

- Exceed requirements of ANSI/TIA-568-C.2 Category 5eabd ISO 11801 Class D channel standards
- Exceed ANSI/TIA568-C.2 Category 5e and ISO 11801 Class D component standards
- Meet requirements of IEEE 802.af and IEEE 802.3at for PoE applications
- Contacts plated with 50 microinches of gold for superior performance
- No punchdown tool required; termination tool (CJT -X) ensures conductors are fully terminated by utilizing a smooth forward motion without impact on critical internal components for maximum reliability
- Orange module base sled designates Category 5e performance
- Terminate 4-pair, 24 – 22 AWG, 100 ohm, solid twisted pair cable
- Universal label is color -coded for T568A and T568B wiring schemes
- Can be clearly identified with optional labels and icons
- Compatible with Mini-Com® Modular Patch Panels, Faceplates, and Surface Mount Boxes

Part Number	CJ588ORY
RoHS Compliancy Status	Compliant
Note	CJ588ORY replaces CJ588OR
Part Description	Category 5e, RJ45, leadframe, 8-position, 8-wire universal module.
Product Type	Leadframe Copper Module
Color	Orange
CE Compliant	No
Modular Jack Type	RJ45
No. of Module Spaces	1
Performance Level	Category 5e/Class D
Pricing Description	Mini-Com Mini-Jack Module, Cat 5e, UTP, 8 pos 8 wire, Universal, Orange
Wiring Scheme	T568A and T568B
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy