THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION – ,– .
© COPYRIGHT – By – ALL RIGHTS RESERVED.

NOTES:
Tolerances cable lengths:

0m to 0.5m	+30mm
0.5m to 1.0m	+50mm
1.0m to 3.0m	+100mm
< 3.0m	+1.5%

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR–15–018514	21DEC2015	TB	BvH
	B1	ECR–16–003945	16MAR2016	GSK	BvH
	B2	ECR–17–005498	17APR2017	GSK	TCC





PVC CABLE	
No./diameter of wires	4 x 0.34 mm²
Wire isolation	PVC (br, wh, bl, bk)
C–track properties	
Jacket	PVC (UL/CSA)
Outer diameter	approx. 5.0 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	–30...+80 °C
Temperature range (mobile)	–5...+80 °C

Contact Layout
Female



Schematic diagram



TECHNICAL DATA	
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)
Operating voltage	24 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 x 1 mm (recommended torque 0.6 Nm) self–securing

PUR CABLE	
No./diameter of wires	4 x 0.34 mm²
Wire isolation	PVC (br, wh, bl, bk)
C–track properties	
Jacket	PUR/PVC (UL/CSA)
Outer diameter	approx. 5.9 mm
Bend radius (moving)	15 x outer diameter
Temperature range (fixed)	–30...+80 °C
Temperature range (mobile)	–5...+70 °C

LENGTH"L"	MATERIAL	JACKET COLOR	TE PN	DESCRIPTION	ITEM
4 pos 10mtr	PVC	Black	1–2273083–4	4x22AWG PVC 10.0m	8
4 pos 5mtr	PVC	Black	1–2273083–3	4x22AWG PVC 5.0m	7
4 pos 3mtr	PVC	Black	1–2273083–2	4x22AWG PVC 3.0m	6
4 pos 1.5mtr	PVC	Black	1–2273083–1	4x22AWG PVC 1.5m	5
4 pos 10mtr	PUR	Black	2273083–4	4x22AWG PUR 10.0m	4
4 pos 5mtr	PUR	Black	2273083–3	4x22AWG PUR 5.0m	3
4 pos 3mtr	PUR	Black	2273083–2	4x22AWG PUR 3.0m	2
4 pos 1.5mtr	PUR	Black	2273083–1	4x22AWG PUR 1.5m	1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL –
FINISH –

DWN SATHISH KUMAR .G 26NOV2013
CHK B.VELDHOVEN 26NOV2013
APVD A.VAN ZANDVOORT 26NOV2013
PRODUCT SPEC 108–19483
APPLICATION SPEC 114–32127
WEIGHT

TE Connectivity

NAME M12 X 1.0 ANGLED SOCKET PIGT A

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C–2273083	—

CUSTOMER DRAWING | SCALE NTS | SHEET 1 OF 1 | REV B2