

## Sales Outline Drawing

Revision

A

## Specifications:

|                                   |                                           |
|-----------------------------------|-------------------------------------------|
| Voice Coil Impedance ( $\Omega$ ) | $8 \pm 15\%$ at 800 Hz / 1.0 V            |
| Rated Input (W)                   | 0.25                                      |
| Max. Input (W)                    | 0.50                                      |
| Lowest Resonance Freq Fo (Hz)     | $500 \pm 20\%$                            |
| Frequency Range (Hz)              | Fo ~ 5000                                 |
| Output S.P.L. (dB)                | $89 \pm 3$ at 1W 1M .8k, 1k, 1.2k, 1.5kHz |
| Magnet Size (mm)                  | $\varnothing 12.5 * 1.5$                  |
| Magnet                            | Ferrite                                   |
| Core Material Mylar               | Black Radial                              |
| Frame Material                    | Metal                                     |
| Options                           | For other options contact factory         |

Dimensions: (units: mm)

ROHS Compliant

