



HSEC8-DV SERIES

VERTICAL EDGE RATE® CARD SOCKET

UL
FILE NO. E111594

CSA
FILE NO. 000921 0 000

Final Inch[®] | 28+
C E R T I F I E D G b p s

POSITIONS PER ROW	A	B
09 ⁺	(4.50).177	(11.80).465
13 ⁺	(6.10).240	(15.00).591
25 ⁺	(6.10).240	(24.60).969
37 ⁺	(18.10).713	(34.20).1346
40	(18.90).744	(36.60).1441
49 ⁺	(22.90).902	(43.80).1724
50	(22.90).902	(44.60).1756
60	(26.90).1059	(52.60).2071
70 ⁺	(26.90).1059	(60.60).2386
80 ⁺	(26.90).1059	(68.60).2701
100 ⁺	(26.90).1059	(84.60).3331

Positions where no dimensions are given do not have keying feature.

* Mates with ECDP Series.

† Available with -01 Card Only.

-K
= (7.01 mm) .276" DIA
Polyimide Film
Pick & Place Pad
(with -01 card)
= (6.25 mm) .246" DIA
Polyimide Film
Pick & Place Pad
(with -03 card)

-BL
= Board Locks
(40, 50, 60, 80 only)
(Other sizes available.
Contact Samtec.)
(Weld tab standard)

-L
= Latching Option
(13, 25, 37, 49 only)
(Weld tab standard)

-L2
= ECDP Latching
(09, 13, 25, 49 only)
(For use with ECDP)
(Weld tab standard)

—WT
= Weld tab

-TR
= Tape & Reel
(09 - 70 only)