Part Number: 50558-7612

Ring Tongue Terminal for 2 AWG, Closed Un-insulated Brazed Barrel, Stud Size 1/4" (M6), Oxygen-Free Copper, Length 38.00mm

Series image - Reference only

Status:	**OBSOLETE**
Replacement:	Contact Molex
Series:	50558
Category:	Ring and Spade Terminals

Go to **Part Detail**▼

CHECK DISTRIBUTOR INVENTORY

Add to My Parts

Email this page

Specifications & Other Documents:

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

EU ELV: Not Relevant
EU RoHS: Compliant
China RoHS:
REACH SVHC: Contains SVHC(2015 June 15): No
Low-Halogen Status: Low-Halogen

RoHS Certificate of Compliance (PDF)
Multiple Part Product Compliance Form

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Japan

Description	Product #
Battery Type Hand Crimper For JIS Terminal	57343-9004

Crimp Quality Equipment
Molex also offers wire strippers, pull testers, shut-height gauges, micro-meters and more

Previously Available Application Tooling
Check our list of old tooling that used to be available for this part

Part Detail

COLLAPSE ALL

General

Status	**Obsolete**
Category	Ring and Spade Terminals
Series	50558
Mil-Spec	N/A
Product Name	R (Ring)
Type	Ring
UPC	800753365162

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	12390.000/mg
Packaging Type	Bag
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Stud Size	1/4" (M6)
Termination Interface: Style	Crimp or Compression
Wire Size AWG	2
Wire Size mm²	26.66-42.42

Material Info

Reference - Drawing Numbers

Product Specification	PS-50555-001
Sales Drawing	SD-50558-001

Copyright 2015