THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST
FB	00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	P	REVISED PER ECO-11-005033	28MAR11	RK	HMR







NOTES;

1. .MATERIAL:HOUSING - 66 NYLON (UL94V-0)
   POST - TIN BRASS



3 Pos.



2 Pos.



SECT. A-A

6-	-6	4-	-6	2-	-6		-6	6	15.8	10.0
6-	-5	4-	-5	2-	-5		-5	5	13.8	8.0
6-	-4	4-	-4	2-	-4		-4	4	11.8	6.0
6-	-3	4-	-3	2-	-3		-3	3	9.8	4.0
6-292156-2		4-292156-2		2-292156-2		292156-2		2	7.8	2.0
BLACK		YELLOW		BLUE		NATURAL		Pos.	B	A
PART NO.										

TOLERANCES UNLESS OTHERWISE SPECIFIED:
10≥* : ±0.2
30≥*>10 : ±0.25
100≥*>30 : ±0.3
ANGEL : ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL 1

FINISH 1

DWN	S.XU	31JAN03
CHK	S.YAO	31JAN03
APVD	T.SASAKI	31JAN03
PRODUCT SPEC	—	
APPLICATION SPEC	—	
WEIGHT	—	

TE Connectivity

NAME
FREE HANGING TYPE RELAY POST HEADER ASS'Y
(AMP CT CONN. 2mm PITCH)

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-292156	—

CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 1 | REV P

1470-19 (3/11)