

TYPE		GT-12QP-3
RATED VOLTAGE	(V)	1.5
# CURRENT CONSUMPTION	(mA)	MAX. 70
COIL RESISTANCE	(Ω)	6.5 1±
# SOUND PRESSURE LEVEL	(dB)	92(TYP)
RESONANCE FREQUENCY	(Hz)	2730
operating voltage	(V)	1-2
operating temperature	(°C)	-20 ~ +60
STORAGE TEMPERATURE	(°C)	-30 ~ +70
WEIGHT	(g)	1

VALUE APPLYING RATED VOLTAGE. (2730Hz,1/2 DUTY CYCLE,SQUARE WAVE)

tolerance: 0.3 ±

SOBERTON INC.	DR.		SCALE	2/1	TITLE	BUZZER	
	CHK.		SHEET		MATERIAL	NORYL	PART NO.
MODEL NO. GT-12QP-3	APP.		UNIT	mm	FINISH		DWG. NO. RP/B

NO	DATE	ECN. NO.
5		
4		
3		
2		
1		