LED PANEL MOUNT INDICATOR

PROMINENT BEZEL, DC OPERATION

MOUNTING HOLE, Ø 8mm

PART NO.	COLOR	VOLTAGE V_{OP} [V] DC	CURRENT $I_{OP\ typ.}$ [mA] DC	LUMI. INTENSITY LED $I_{V\ typ.}$ [mcd]	DOMINANT WAVELENGTH λ_D [nm]
SATIN CHROME BEZEL					
WL-19040251	GREEN	12V	20	40	568
WL-19040252	YELLOW	12V	20	40	588
WL-19040253	RED	12V	20	80	625
WL-19040257	BLUE	12V	20	90	466
WL-1904025W	WHITE	12V	20	450	*
WL-19040351	GREEN	24V	20	40	568
WL-19040352	YELLOW	24V	20	40	588
WL-19040353	RED	24V	20	80	625
WL-19040357	BLUE	24V	20	90	466
WL-1904035W	WHITE	24V	20	450	*
WL-19040451	GREEN	28V	20	40	568
WL-19040452	YELLOW	28V	20	40	588
WL-19040453	RED	28V	20	80	625
WL-19040457	BLUE	28V	20	90	466
WL-1904045W	WHITE	28V	20	450	*
BLACK CHROME BEZEL					
WL-19041251	GREEN	12V	20	40	568
WL-19041252	YELLOW	12V	20	40	588
WL-19041253	RED	12V	20	80	625
WL-19041257	BLUE	12V	20	90	466
WL-1904125W	WHITE	12V	20	450	*
WL-19041351	GREEN	24V	20	40	568
WL-19041352	YELLOW	24V	20	40	588
WL-19041353	RED	24V	20	80	625
WL-19041357	BLUE	24V	20	90	466
WL-1904135W	WHITE	24V	20	450	*
WL-19041451	GREEN	28V	20	40	568
WL-19041452	YELLOW	28V	20	40	588
WL-19041453	RED	28V	20	80	625
WL-19041457	BLUE	28V	20	90	466
WL-1904145W	WHITE	28V	20	450	*

*Chromaticity coordinates X=0.31 Y=.032

NOTES

1. Maximum panel thickness 4mm
2. Storage temperature T_{STG}: -25°C – +80°C
3. Ambient temperature T_A: -20°C – +60°C
4. DC operation only
5. Voltage tolerance V_{OP}: ±10%
6. Electro-optical ratings at T_A=25°C
7. Degree of protection: IP67 in accordance to DIN EN 60529 when using the supplied gasket
8. Mounting hole 8 + 0.2mm
9. 2.8 x 0.8mm terminals are standard
10. Due to production tolerances, slight color variations may be detected within individual consignments
11. Supplied with mounting hardware; 1) gasket, 2) spring washer, and 3) M8 nut
12. CAUTION: Do not solder directly to terminals

CERTIFICATIONS

RoHS COMPLIANT

DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in mm

OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

P: (714) 545-5560 F: (714) 545-6093
W: WWW.WAMCOINC.COM E: INFO@WAMCOINC.COM