Product Data Sheet

QO125

Miniature Circuit Breaker (QO) Standard, 25A, 1-Pole, 120/240 Vac, 1-Phase, 10kA

SQUARE D by Schneider Electric

List Price	$29.10 USD
Availability	**Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Approvals	UL Listed - CSA Certified
Circuit Breaker Type	Standard
For Use With	QO Load Centers, NQ & NQOD Panelboards/Interiors and Speed-D switchboard distribution panels
Ampere Rating	25A
Features	VISI-TRIP trip indication
HACR Rated	Yes
General Application	Provides overload and short circuit protection
Type	QO
Number of Poles	1-Pole
Wire Size	#14 to #8 AWG(Al/Cu)
Phase	1-Phase
Height	3.00 Inches
Width	0.75 Inches
Marketing Trade Name	QO
Depth	2.91 Inches
Short Circuit Current Rating	10kA
Voltage Rating	120/240VAC
Space Required	1
Mounting Type	Plug-On
Terminal Type	Pressure Plate

Shipping and Ordering

Category	00004 - Circuit Breakers, 1 Pole: 10 - 30 Amp, 2 Pole: 10 - 60 Amp, Type QO & QOT
Discount Schedule	DE2A
GTIN	00785901010418
Package Quantity	40
Weight	0.26 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Generated: 08/08/2012 04:39:32

© 2012 Schneider Electric. All rights reserved.