




CT20R-2024-01-GF



CC20R-2024-01-S

SIZE 20 CRIMP CONTACTS CT20, CC20 SERIES

Contact for:
DSM-CP

SPECIFICATIONS

For complete specifications
see www.samtec.com?CT20

Contact Material:

Brass

Plating:

Au or Sn over 50µ" (1,27µm) Ni

Wire:

28 to 20 AWG

RoHS Compliant:

Yes

APPLICATION SPECIFIC OPTION

Assembly with wire
and DSM-CP available.
See DSSD & DSMD Series

Note: Some lengths, styles
and options are non-standard,
non-returnable.

TYPE

CT20L

= Terminal, Loose

CT20R

= Terminal, Full Reel
(10,000 Parts per Reel)

WIRE SIZE

-2024

= 24 to 20 AWG

-2428

= 28 to 24 AWG

01

PLATING

-S


= 30µ" (0,76µm) Gold on contact, Tin on tail

-GF

= Gold Flash on mating area, Gold Flash on balance

-T

= Tin



ALSO AVAILABLE

Assembly tooling.
Contact atg@samtec.com

WIRE SIZE	INSULATION RANGE
-2024	(1,27) .050 MAX
-2428	(1,02) .040 MAX

Contact for:
DSM-CP

SPECIFICATIONS

For complete specifications
see www.samtec.com?CC20

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over 50µ" (1,27µm) Ni

Wire:

28 to 20 AWG

RoHS Compliant:

Yes

APPLICATION SPECIFIC OPTION

Assembly with wire
and DSM-CP available.
See DSSD & DSMD Series

Note: Some lengths, styles
and options are non-standard,
non-returnable.

TYPE

CC20L

= Contact, Loose

CC20R

= Contact, Full Reel
(10,000 Parts per Reel)

WIRE SIZE

-2024

= 24 to 20 AWG

-2428

= 28 to 24 AWG

01

PLATING

-S


= 30µ" (0,76µm) Gold on contact, Tin on tail

-GF

= Gold Flash on mating area, Gold Flash on balance

-T

= Tin



ALSO AVAILABLE

Assembly tooling.
Contact atg@samtec.com

WIRE SIZE	INSULATION RANGE
-2024	(1,27) .050 MAX
-2428	(1,02) .040 MAX

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 • Fax: 812-948-5047
 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0 • Fax: +49 (0) 89 / 89460-299
 SAMTEC JAPAN • Tel: +66-84477280 • Fax: +66-847420413
 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 • Fax: 65 6841-1502
 SAMTEC HONG KONG • Tel: 852-26904858 • Fax: 852-26904842
 SAMTEC SILICON VALLEY • Tel: 408-395-5900 • Fax: 408-395-1520
 SAMTEC FRANCE • Tel: 01 60 95 06 60 • Fax: 01 60 95 06 61
 SAMTEC ISRAEL • Tel: 972-3-7526600 • Fax: 972-3-7526690
 SAMTEC CHINA • Tel: 86-21-61103766 • Fax: 86-21-53854047
 SAMTEC SOUTH AFRICA • Tel: 27 11 4528112 • Fax: 27 86 6714432
 SAMTEC UK • Tel: 01236 739292 • Fax: 01236 727113
 SAMTEC ITALY • Tel: 39 039 6890337 • Fax: 39 039 6890315
 SAMTEC INDIA • Tel: 91 80 306 21 612 • Fax: 91 80 4152 8187
 SAMTEC TAIWAN • Tel: 886 02 2698-3367 • Fax: 886 02 8698-2159
 SAMTEC ANZ • Tel: 613 9512 7747 • Fax: 613 9512 7745