

Item # 41SH12, Air-Seal Foot Switch



Air-Seal Foot Switch

The Air-Seal foot switch offers the benefit of isolating the electrically live snap switch from the floor, which also offers environmental protection. Other benefits include long trouble free life and application versatility. The Air-Seal foot switch series combines a foot operated air bulb mounted in our strong, steel Compact housing and a remotely located air operated electric snap switch. The Air-Seal is available in either momentary or maintained versions, with SPDT snap switch. A 10 foot 1/8" ID PVC tubing connects the foot pedal to the remote airswitch, which is equipped with a 9/16" UNF bulkhead mount. The tubing is connected at the foot switch end using a molded on strain relief grommet providing superior pull out protection.

SPECIFICATIONS

Description	Momentary
Circuit	SPDT
Form	C
Operating Temperature Range	10 to 120 °F
Electrical Rating	20 A 125-250 VAC 1 H.P. 125 VAC 2 H.P. 250 VAC
Standards	EN 60529 Degree of Protection IPXX Master Actuator, EN 60529 Degree of Protection IP00 Snap Switch
Size	2 7/8 x 4 1/2 x 1 1/8 Inch
Weight	1/2 lbs
Note	The operating temperature range will vary with different lengths of tubing. Please consult the factory for details.