







Section A-A

NOTES:

MATERIAL
1.Insulator Material:PBT+30%GF(UL94V-0)
2.Contact Material : Brass
3.Contact Plating :
AWP xx-8240-T : Gold flash over Ni
AWP xx-8540-T : Tin over Ni

ELECTRICAL
1.Current Rating : 3AMP
2.Voltage Rating : 500V AC/DC
3.Withstand Voltage : 1000V AC/DC
4.Contact Resistance : 20mΩ max
5.Insulation Resistance: 1000MΩ min

ENVIRONMENTAL
1.Operation Temperature: -40°C to +105°C
2.Packing: Tray

② 6P-8P Without Slot "M" and "N"
10P-12P With Slot "M", Without "N"
14P-64P With Slot "M" and "N"

RoHS compliant
unit:mm

Scale	Free
TOLERANCE	
X.	±0.35
.X	±0.25
.XX	±0.20
.XXX	±0.15
DIM	TOL
Angle	TOL

Id.	modification	Date	Name
③	Update Description	15.03.2022	Winnie
②	Drawn	28.03.2013	Dean
①	Drawn	21.12.2009	Dean

	Date	Name
Drawn	21.12.2009	Dean
Approved	28.03.2013	Hellwig

ASSMANN WSW components

Description: ③ DIN 41651 / IDC-socket
2.54mm pitch
without central polarisation

ASSMANN WSW-NO.
AWP xx-8x40-T

Drawing-No.
ASS 2261A CO
rev03

Customer-No.

SHEET
1 / 1