THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST
G	02

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED PER ECO-11-004917	11MAR11	RK	HMR

AMP WIRE RANGE	Listed
0.25-1.65 SOLID OR STRANDED	0.25-1.65 SOLID OR STRANDED



1. STAMP AMP 22-16*
   LOCATE APPROX AS SHOWN
2. FOR WIRE INSULATION DIA 2.7-3.6
3. TONGUE THK IS 0.8±0.07
4. BODY: COPPER PER ASTM B-152
   TIN PLATED PER ASTM B-545
5. SLEEVE: PVC, RED
6. APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.

QTY	PACKAGE TYPE	PART NO
5,000	ON TAPE, REEL	2-165008-1
1,000	LOOSE PIECE	165008-0

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM ~~INCHES~~

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± 0.2
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± 1°

MATERIAL: SEE NOTES

FINISH: SEE NOTES

DWN	JR RUTH	27OCT03
CHK	T MICHIELUTTI	27OCT03
APVD	T MICHIELUTTI	27OCT03
PRODUCT SPEC	—	
APPLICATION SPEC	—	
WEIGHT	—	

TE Connectivity

NAME: TERMINAL, SPADE, PLASTI-GRIP, WIRE SIZE, 22-16 AWG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-165008	—

CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 1 | REV D1