插頭部件 (Plug Component)			頭部剝皮尺寸 (Dimensions)			線材規格 (Wire Styls)	尾部剝皮尺寸 (Dimensions)			尾插部件 (Connector Component)		
顏色(Color)	零件描述(Component)	Qty.	內剝(Strip)	外剝(ROJ)	顏色(Color)	SPT-2 18AWG*2C 105°C 黑色 (BLACK) Length : 2000±50 (79"±2")	外剝(R.O.J)	內剝(Strip)	顏色(Color)	規格描述(Instruction)	Qty.	顏色(Color)
35P 黑色 (Black)	ME-101A (1-15P,Non-Polarized)	1	6^{+1}_{-0}	15 ± 2	黑/Black(L)		15 ±2	5^{+1}_{-0}	黑/Black(L)	FM-1FP (IEC 60320, C7, Polarized, 10A 125V~)	1	35P 黑色 (Black)
鍍鎳 (Nickel-Plated)	(8.0/6.3) 極性端子97662-1 (Polarized Solid Blades)	2	6^{+1}_{-0}	15 ± 2	白/White(N)		15 ±2	5^{+1}_{-0}	白/White(N)	O-Type Receptacle Terminal	2	銅本色 (Brass-Natural)





ME-101A (NEMA 1-15P)
(Dimensions of Plug Face)



SPT-2 18AWGx2C截面圖
(Wire Cross-Section)



B-C2 扎線圖示 (Tied Loop Hank Detail)



FM-1FP (IEC 320, C7, Polarized)
(Dimensions of Connector Face)

REV	DATE	REVISE CONTENT
A	08/30-2012	The first edition is issued and drawing.

NOTE :
1 、Hi-Pot Test : 1500V/1Sec ; <0.5mA.
2 、Insulation Resistance Test : DC 500/min>100 meg-ohm.
3 、Continuity & Polarization Test : No short circuit, break circuit, displacement.
4 、Each end terminal shall be capable of withstanding a pull of 25lbs for 1 minutes without loosening.
5 、Strain relief shall be capable of withstanding a pull of 35lbs for 1 minutes without loosening.
6 、All material according to Non-toxic standard.(Material must be RoHS compliant.)
7 、"FMC" logo maybe present on 1-15P.

線材印字 (Wire Printed)	充實, 油墨印字 (Un-Fillers, Printing Ink)		
包裝方式 (Packing)		DRAWN	*Chu8..*
Tied Hank	See Hank Detail		
Carton Size	480 x 320 x 180		
Pack Number	100 pcs/ UL Laster Labels	DATE	08/30-2012
Carton Print	See Purchase Order		
TYPE	NEMA 1-15P Polarized to IEC 60320, C7 Power Supply Cord		
DRAWNING NO.	098MM1016	REV	A

CnC Tech, LLC
Industrial Cable and Connector Technology

CUSTOMER	CnC		
P/N No.	800-1804-2-SPT2-BL-00200		
MATERIAL	PVC	UNIT	㎜
Customer Approval			

業務校閱：
品管校閱：