

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOCADDIST39

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	H	REVISED PER ECO-15-008006	17NOV2015	NK	MM

A SPACES @ 2.54[.100] = B

2.54
[.100]
TYP

C MAX

3

7.49
[.295]

AMP

12.19±0.20
[.480±.008]

1

NO. OF POSITIONS PERTAINS TO THE HOUSING SIZE.

2

THIS COVER WILL MATE WITH COVER HALVES=102537, 102540 & 102541.

3

CENTER TOOTH OMITTED(SEE TABLE)

4

OBSOLETE PART NUMBER

5

MATERIAL: FLAME RETARDANT THERMOPLASTIC
COLOR: BLACK.

—	88.90[3.500]	88.90[3.500]	35	72	4	3-102823-1
—	86.36[3.400]	86.36[3.400]	34	70	4	3-102823-0
—	83.82[3.300]	83.82[3.300]	33	68	4	2-102823-9
—	81.28[3.200]	81.28[3.200]	32	66	4	2-102823-8
—	78.74[3.100]	78.74[3.100]	31	64	4	2-102823-7
—	76.20[3.000]	76.20[3.000]	30	62	4	2-102823-6
—	73.66[2.900]	73.66[2.900]	29	60	4	2-102823-5
—	71.12[2.800]	71.12[2.800]	28	58	4	2-102823-4
—	68.58[2.700]	68.58[2.700]	27	56	4	2-102823-3
—	66.04[2.600]	66.04[2.600]	26	54	4	2-102823-2
—	63.50[2.500]	63.50[2.500]	25	52	4	2-102823-1
—	60.96[2.400]	58.42[2.300]	23	48	4	2-102823-0
—	58.42[2.300]	55.88[2.200]	22	46	4	1-102823-9
—	55.88[2.200]	53.34[2.100]	21	44	4	1-102823-8
—	53.34[2.100]	50.80[2.000]	20	42	4	1-102823-7
—	48.26[1.900]	45.72[1.800]	18	38	4	1-102823-6
—	45.72[1.800]	43.18[1.700]	17	36	4	1-102823-5
—	43.18[1.700]	40.64[1.600]	16	34		1-102823-4
—	40.64[1.600]	38.10[1.500]	15	32		1-102823-3
3	38.10[1.500]	35.56[1.400]	14	30		1-102823-2
3	35.56[1.400]	33.02[1.300]	13	28		1-102823-1
3	33.02[1.300]	30.48[1.200]	12	26		1-102823-0
3	30.48[1.200]	27.94[1.100]	11	24		102823-9
3	27.94[1.100]	25.40[1.000]	10	22		102823-8
3	20.32[.800]	17.78[.700]	7	16		102823-7
3	17.78[.700]	15.24[.600]	6	14		102823-6
3	15.24[.600]	12.70[.500]	5	12		102823-5
3	25.40[1.000]	22.86[.900]	9	20	4	102823-4
—	63.50[2.500]	60.96[2.400]	24	50		102823-3
—	50.80[2.000]	48.26[1.900]	19	40	4	102823-2
3	22.86[.900]	20.32[.800]	8	18		102823-1

REMARK	C	B	A	NO. OF POSN	PART NUMBER
--------	---	---	---	-------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± 0.13[.005]

4 PLC ± -

ANGLES ± -

FINISH

MATERIAL

5

DWN RAGHAVENDRA 06MAR09

CHK JEFFREY GESFORD 06MAR09

APVD JEFFREY GESFORD 06MAR09

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

SIZE A2

CAGE CODE 00779

DRAWING NO C=102823

RESTRICTED TO

SCALE 5:1

SHEET 1 OF 1

REV H

TE Connectivity

COVER-HALF, MASS TERMINATION, AMPMODU, LOW PROFILE, .100 CL

1471-9 (3/11)