






REV.	DATE	DESCRIPTION
NC	05/25/00	INITIAL RELEASE
A	12/11/07	UPDATE DRAWING FORMAT



RECOMMENDED CABLE
STRIPPING DIM'S.



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS		DATE		Amphenol Connex								
7						DRAWN	G.R.S.	12/11/07										
6	FERRULE	COPPER	GOLD	1		CHECKED												
5	RETAINER RING	BER. COPPER	GOLD	1		ISSUED				PART DESCRIPTION								
4	BARREL	BRASS	GOLD	1		SHEET	1 OF 1				MMCX STRAIGHT DIRECT SOLDER PLUG (FOR .047” SEMI–RIGID CABLE)							
3	CONTACT PIN	BRASS	GOLD	1						PART NO.								
2	INSULATOR	TEFLON	NATURAL	1						262127								
1	BODY	BRASS	GOLD	1						DWG. NO.		262127.DWG	REV.	A	SIZE	A	SCALE	NA
DESCRIPTION		MATERIAL	FINISH	QTY		DO NOT SCALE DRAWING		CAD FILE		C:/262/262127.DWG								