



FCIconnect.com

Copyright FCI.

1

2

## List of "SFW\_\_R-1/2STE1LF" customer document

| DOCUMENT NO. | LIST                                                                                |
|--------------|-------------------------------------------------------------------------------------|
| SC-SFW10     | SPEC.                                                                               |
| JSA95854     | CAT.NO.TABLE FOR 1mm SPACING SMT CONNECTOR (SFW__R-1/2ST__LF)                       |
| JSA95855     | 1mm SPACING SMT CONNECTOR (SFW__R-1ST__LF)                                          |
| JSA95856     | 1mm SPACING SMT CONNECTOR (SFW__R-2ST__LF)                                          |
| JSA95857     | CAT.NO.TABLE FOR PLASTIC TAPE PACKAGED 1mm SPACING SMT CONNECTOR (SFW__R-1/2STE1LF) |
| JSA95858     | PLASTIC TAPE PACKAGED 1mm SPACING SMT CONNECTOR (SFW__R-1STE1LF)                    |
| JSA95859     | PLASTIC TAPE PACKAGED 1mm SPACING SMT CONNECTOR (SFW__R-2STE1LF)                    |
| JSA91605     | RECOMMENDED CABLE (FPC) (SFW__R-1/2ST__)                                            |
| JSA91604     | RECOMMENDED CABLE (FFC) (SFW__R-1/2ST__)                                            |
| GS-20-129    | HANDLING PROCEDURES                                                                 |

|               |  |  |  |                                                 |  |            |  |                     |  |                                             |  |
|---------------|--|--|--|-------------------------------------------------|--|------------|--|---------------------|--|---------------------------------------------|--|
| mat'l. code - |  |  |  | surface ISO 1302 58/ tolerance ISO 406 ISO 1101 |  | projection |  | product family 58RF |  | CODE JP                                     |  |
| ltr           |  |  |  | ecn no                                          |  | dr         |  | date                |  | title                                       |  |
| A             |  |  |  | J05-0055                                        |  | H.T        |  | '05/2/4             |  | 1mm SPACING FPC/FFC CONNECTOR DOCUMENT LIST |  |
| B             |  |  |  | J06-0398                                        |  | H.T        |  | 9/26/'06            |  | (Cat. No. : SFW__R-1/2STE1LF)               |  |
| C             |  |  |  | J09-0358                                        |  | M.Y        |  | 2009-10-5           |  |                                             |  |
| D             |  |  |  | J09-0380                                        |  | M.Y        |  | 2009-10-27          |  |                                             |  |
|               |  |  |  |                                                 |  |            |  |                     |  | dwg no sheet 1 of 1 size                    |  |
|               |  |  |  |                                                 |  |            |  |                     |  | JSA 96336 A4                                |  |
|               |  |  |  |                                                 |  |            |  |                     |  | type Product Customer Drawing               |  |
| sheet index   |  |  |  | revision sheet                                  |  | D 1        |  |                     |  | Rev. D                                      |  |

form: A4

1

2

PDM: Rev:D

STATUS: Released

Printed: Nov 01, 2009

## CAT. NO. &amp; DIMENSIONS

| NO. OF CONTACTS (n) | CAT. NO.         | DIMENSIONS (NOTE2) |         |         |         |
|---------------------|------------------|--------------------|---------|---------|---------|
|                     |                  | A ± 0.2            | B ± 0.2 | C ± 0.2 | D ± 0.1 |
| 4                   | SFW4R-1/2ST__LF  | 9.8                | 8.6     | 3.0     | 5.3     |
| 5                   | SFW5R-1/2ST__LF  | 10.8               | 9.6     | 4.0     | 6.3     |
| 6                   | SFW6R-1/2ST__LF  | 11.8               | 10.6    | 5.0     | 7.3     |
| 7                   | SFW7R-1/2ST__LF  | 12.8               | 11.6    | 6.0     | 8.3     |
| 8                   | SFW8R-1/2ST__LF  | 13.8               | 12.6    | 7.0     | 9.3     |
| 9                   | SFW9R-1/2ST__LF  | 14.8               | 13.6    | 8.0     | 10.3    |
| 10                  | SFW10R-1/2ST__LF | 15.8               | 14.6    | 9.0     | 11.3    |
| 11                  | SFW11R-1/2ST__LF | 16.8               | 15.6    | 10.0    | 12.3    |
| 12                  | SFW12R-1/2ST__LF | 17.8               | 16.6    | 11.0    | 13.3    |
| 13                  | SFW13R-1/2ST__LF | 18.8               | 17.6    | 12.0    | 14.3    |
| 14                  | SFW14R-1/2ST__LF | 19.8               | 18.6    | 13.0    | 15.3    |
| 15                  | SFW15R-1/2ST__LF | 20.8               | 19.6    | 14.0    | 16.3    |
| 16                  | SFW16R-1/2ST__LF | 21.8               | 20.6    | 15.0    | 17.3    |
| 17                  | SFW17R-1/2ST__LF | 22.8               | 21.6    | 16.0    | 18.3    |
| 18                  | SFW18R-1/2ST__LF | 23.8               | 22.6    | 17.0    | 19.3    |
| 19                  | SFW19R-1/2ST__LF | 24.8               | 23.6    | 18.0    | 20.3    |
| 20                  | SFW20R-1/2ST__LF | 25.8               | 24.6    | 19.0    | 21.3    |
| 21                  | SFW21R-1/2ST__LF | 26.8               | 25.6    | 20.0    | 22.3    |
| 22                  | SFW22R-1/2ST__LF | 27.8               | 26.6    | 21.0    | 23.3    |
| 23                  | SFW23R-1/2ST__LF | 28.8               | 27.6    | 22.0    | 24.3    |
| 24                  | SFW24R-1/2ST__LF | 29.8               | 28.6    | 23.0    | 25.3    |
| 25                  | SFW25R-1/2ST__LF | 30.8               | 29.6    | 24.0    | 26.3    |
| 26                  | SFW26R-1/2ST__LF | 31.8               | 30.6    | 25.0    | 27.3    |
| 27                  | SFW27R-1/2ST__LF | 32.8               | 31.6    | 26.0    | 28.3    |
| 28                  | SFW28R-1/2ST__LF | 33.8               | 32.6    | 27.0    | 29.3    |
| 29                  | SFW29R-1/2ST__LF | 34.8               | 33.6    | 28.0    | 30.3    |
| 30                  | SFW30R-1/2ST__LF | 35.8               | 34.6    | 29.0    | 31.3    |

CAT. NO.

SFW (n) R - 1 ST \_\_ LF

SERIES NAME

NO. OF CONTACTS

RIGHT ANGLE TYPE

FOR FPC/FFC, CONTACT DIRECTION

1. LOWER CONTACT TYPE

2. UPPER CONTACT TYPE

FOR AUTOMATIC MOUNTING (SMT)

PACKAGE STYLE



LEAD FREE

## NOTES


1. THIS PRODUCT IS THE CONNECTOR USED FOR FPC/FFC AND COPS WITH AUTOMATIC MOUNTING (SMT).

2. SEE PART DRAWINGS FOR DIMENSIONS A~D.

3. A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

|             |          |      |          |                                              |             |                                                                                           |                                                                                                |                                                                                |  |  |  |         |  |  |  |         |
|-------------|----------|------|----------|----------------------------------------------|-------------|-------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------|--|--|--|---------|--|--|--|---------|
| mat'l. code |          |      |          | surface 58 / tolerance ISO 1302 406 ISO 1101 |             |                                                                                           | projection  | product family 58RF                                                            |  |  |  | CODE JP |  |  |  |         |
| ltr         | ecn no   | dr   | date     | tolerances unless otherwise specified        |             |                                                                                           |                                                                                                | title CAT. NO. TABLE FOR 1mm SPACING SMT CONNECTOR (Cat. No. SFW__R-1/2ST__LF) |  |  |  |         |  |  |  |         |
| AA          | J05-0055 | H.T  | 05-02-04 | angles                                       | linear      |        |                                                                                                |                                                                                |  |  |  |         |  |  |  |         |
| AB          | J06-0398 | H.T  | 06-09-26 |                                              |             |                                                                                           |                                                                                                |                                                                                |  |  |  |         |  |  |  |         |
| AC          | S08-0276 | DGOH | 08-08-22 |                                              |             | scale  |                                                                                                |                                                                                |  |  |  |         |  |  |  |         |
|             |          |      |          | dr                                           | H. TAKAKURA | 06-09-26                                                                                  |             | dwg no sheet 1 of 1                                                            |  |  |  | size A4 |  |  |  |         |
|             |          |      |          | enr                                          | H. TAKAKURA | 06-09-26                                                                                  |                                                                                                | JSA 95854                                                                      |  |  |  |         |  |  |  |         |
|             |          |      |          | chr                                          | DENNIS GOH  | 08-08-22                                                                                  |                                                                                                |                                                                                |  |  |  |         |  |  |  |         |
|             |          |      |          | appd                                         | JOEY NG     | 08-08-22                                                                                  |                                                                                                |                                                                                |  |  |  |         |  |  |  |         |
| sheet index | revision | AC   |          |                                              |             |                                                                                           |                                                                                                |                                                                                |  |  |  |         |  |  |  | Rev. AC |
|             | sheet    | 1    |          |                                              |             |                                                                                           |                                                                                                |                                                                                |  |  |  |         |  |  |  |         |

SC-SFW10 JSA95855 95856 95857 95858 95859 91605 91604 1




| PT. NO. | PARTS NAME     | MATERIAL                             | Q'TY | NOTE          |
|---------|----------------|--------------------------------------|------|---------------|
| 1       | HOUSING        | PPS RESIN GLASS REINFORCED (UL94V-0) | 1    | COLOR : BROWN |
| 2       | SLIDER         | PPS RESIN GLASS REINFORCED (UL94V-0) | 1    | COLOR : BLACK |
| 3       | CONTACT        | PHOSPHOR BRONZE                      | n    | PLATING : TIN |
| 4       | MOUNTING PLATE |                                      | 2    |               |


n : NO. OF CONTACTS

#### NOTES

1. THIS PRODUCT IS THE CONNECTOR USED FOR FPC/FFC AND CYPES WITH AUTOMATIC MOUNTING (SMT).
2. FLATNESS FOR CONTACT TERMINAL HOUSING MUST BE WITHIN TOLERANCE IN Z PORTION DETAILED DRAWING.
3. THIS PRODUCT IS LOWER CONTACT TYPE CONNECTOR.
4. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
5. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A REFLOW SOLDERING OVEN.
3. A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING. REVISION.

#### RECOMMENDED PC BOARD LAYOUT (COMPONENT SIDE)



|             |          |      |          |                                       |                    |                                                                                     |                                                                 |         |
|-------------|----------|------|----------|---------------------------------------|--------------------|-------------------------------------------------------------------------------------|-----------------------------------------------------------------|---------|
| mat'l. code |          |      |          | surface 58                            | tolerance ISO 1302 | projection                                                                          | product family 58RF                                             | CODE JP |
| ltr         | ecn no   | dr   | date     | tolerances unless otherwise specified | ISO 406            |  | title<br>1mm SPACING SMT CONNECTOR<br>(Cat. No. SFW__R-1ST__LF) |         |
| AA          | J04-0180 | H.T  | 04-07-02 | angles                                | ISO 1101           |                                                                                     |                                                                 |         |
| AB          | J05-0055 | H.T  | 05-02-04 | linear                                | ±0.2               | mm                                                                                  | dwg no sheet 1 of 1 size<br>JSA 95855 A4                        |         |
| AC          | J05-0736 | H.T  | 05-10-28 |                                       |                    | scale                                                                               |                                                                 |         |
| AD          | J06-0398 | H.T  | 06-09-26 | dr                                    | H. TAKAKURA        | 06-09-26                                                                            | type Product Customer Drawing                                   |         |
| AE          | S08-0276 | DGOH | 08-08-22 | enr                                   | H. TAKAKURA        | 06-09-26                                                                            |                                                                 |         |
|             |          |      |          | chr                                   | DENNIS GOH         | 08-08-22                                                                            | Rev. AE                                                         |         |
|             |          |      |          | appd                                  | JOEY NG            | 08-08-22                                                                            |                                                                 |         |
| sheet index | revision | AE   | 1        |                                       |                    |                                                                                     |                                                                 |         |


SC\_SFW10 JSA95854  
form: A4

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI.



FCIconnect.com

Copyright FCI.




| PT. NO. | PARTS NAME     | MATERIAL                             | Q'TY | NOTE          |
|---------|----------------|--------------------------------------|------|---------------|
| 1       | HOUSING        | PPS RESIN GLASS REINFORCED (UL94V-0) | 1    | COLOR : BROWN |
| 2       | SLIDER         | PPS RESIN GLASS REINFORCED (UL94V-0) | 1    | COLOR : BLACK |
| 3       | CONTACT        | PHOSPHOR BRONZE                      | n    | PLATING : TIN |
| 4       | MOUNTING PLATE |                                      | 2    |               |

n : NO. OF CONTACTS

#### NOTES

1. THIS PRODUCT IS THE CONNECTOR USED FOR FPC/FFC AND COPEs WITH AUTOMATIC MOUNTING (SMT).
2. FLATNESS FOR CONTACT TERMINAL HOUSING MUST BE WITHIN TOLERANCE IN Z PORTION DETAILED DRAWING.
3. THIS PRODUCT IS UPPER CONTACT TYPE CONNECTOR.
4. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER?COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
5. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A REFLOW SOLDERING OVEN.
6. A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

#### RECOMMENDED PC BOARD LAYOUT (COMPONENT SIDE)



|             |          |      |          |                                       |                    |            |                                                                 |         |
|-------------|----------|------|----------|---------------------------------------|--------------------|------------|-----------------------------------------------------------------|---------|
| mat'l. code |          |      |          | surface 58                            | tolerance ISO 1302 | projection | product family 58RF                                             | CODE JP |
|             |          |      |          | ISO 406                               | ISO 1101           |            | title<br>1mm SPACING SMT CONNECTOR<br>(Cat. No. SFW__R-2ST__LF) |         |
|             |          |      |          | tolerances unless otherwise specified | ±0.2               |            |                                                                 |         |
| ltr         | ecn no   | dr   | date     | angles                                | linear             | mm         | dwg no sheet 1 of 1 size<br>JSA 95856 A4                        |         |
| AA          | J04-0180 | H.T  | 04-07-02 |                                       |                    |            |                                                                 |         |
| AB          | J05-0055 | H.T  | 05-02-04 |                                       |                    |            | type Product Customer Drawing                                   |         |
| AC          | J05-0736 | H.T  | 05-10-28 |                                       |                    | scale X    |                                                                 |         |
| AD          | J06-0398 | H.T  | 06-09-26 | dr                                    | H. TAKAKURA        | 06-09-26   | Rev. AE                                                         |         |
| AE          | S08-0276 | DGOH | 08-08-22 | enr                                   | H. TAKAKURA        | 06-09-26   |                                                                 |         |
|             |          |      |          | chr                                   | DENNIS GOH         | 08-08-22   |                                                                 |         |
|             |          |      |          | appd                                  | JOEY NG            | 08-08-22   |                                                                 |         |
| sheet index | revision | AE   |          |                                       |                    |            |                                                                 |         |
| sheet       | 1        |      |          |                                       |                    |            |                                                                 |         |

SC\_SFW10 JSA95854  
form: A4

## CAT. NO. &amp; DIMENSIONS

| NO. OF CONTACTS (n) | CAT. NO. (NOTE2)  | DIMENSIONS (NOTE3) |         |         |
|---------------------|-------------------|--------------------|---------|---------|
|                     |                   | E ± 5              | F ± 0.3 | G ± 0.1 |
| 4                   | SFW4R-1/2STE1 LF  | 20.4               | 16      | —       |
| 5                   | SFW5R-1/2STE1 LF  | 28.4               | 24      | —       |
| 6                   | SFW6R-1/2STE1 LF  | 28.4               | 24      | —       |
| 7                   | SFW7R-1/2STE1 LF  | 28.4               | 24      | —       |
| 8                   | SFW8R-1/2STE1 LF  | 28.4               | 24      | —       |
| 9                   | SFW9R-1/2STE1 LF  | 28.4               | 24      | —       |
| 10                  | SFW10R-1/2STE1 LF | 28.4               | 24      | —       |
| 11                  | SFW11R-1/2STE1 LF | 28.4               | 24      | —       |
| 12                  | SFW12R-1/2STE1 LF | 28.4               | 24      | —       |
| 13                  | SFW13R-1/2STE1 LF | 36.4               | 32      | 28.4    |
| 14                  | SFW14R-1/2STE1 LF | 36.4               | 32      | 28.4    |
| 15                  | SFW15R-1/2STE1 LF | 36.4               | 32      | 28.4    |
| 16                  | SFW16R-1/2STE1 LF | 36.4               | 32      | 28.4    |
| 17                  | SFW17R-1/2STE1 LF | 48.4               | 44      | 40.4    |
| 18                  | SFW18R-1/2STE1 LF | 48.4               | 44      | 40.4    |
| 19                  | SFW19R-1/2STE1 LF | 48.4               | 44      | 40.4    |
| 20                  | SFW20R-1/2STE1 LF | 48.4               | 44      | 40.4    |
| 21                  | SFW21R-1/2STE1 LF | 48.4               | 44      | 40.4    |
| 22                  | SFW22R-1/2STE1 LF | 48.4               | 44      | 40.4    |
| 23                  | SFW23R-1/2STE1 LF | 48.4               | 44      | 40.4    |
| 24                  | SFW24R-1/2STE1 LF | 48.4               | 44      | 40.4    |
| 25                  | SFW25R-1/2STE1 LF | 48.4               | 44      | 40.4    |
| 26                  | SFW26R-1/2STE1 LF | 48.4               | 44      | 40.4    |
| 27                  | SFW27R-1/2STE1 LF | 48.4               | 44      | 40.4    |
| 28                  | SFW28R-1/2STE1 LF | 60.4               | 56      | 52.4    |
| 29                  | SFW29R-1/2STE1 LF | 60.4               | 56      | 52.4    |
| 30                  | SFW30R-1/2STE1 LF | 60.4               | 56      | 52.4    |

CAT. NO.

SFW (n) R - 1 ST E1 LF

SERIES NAME

NO. OF CONTACTS

RIGHT ANGLE TYPE

FOR FPC/FFC, CONTACT DIRECTION

1. LOWER CONTACT TYPE
2. UPPER CONTACT TYPE

FOR AUTOMATIC MOUNTING (SMT)

TAPE PACKAGING

LEAD FREE

## NOTES

1. THIS PRODUCT IS THE CONNECTOR USED FOR FPC/FFC AND COPELS WITH AUTOMATIC MOUNTING (SMT).
2. THIS CATALOG NO. INDICATES PLASTIC TAPE PACKAGED CONNECTOR.
3. SEE PART DRAWINGS FOR DIMENSIONS E~G.
4. A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

|             |          |      |          |                                       |                              |                                                                                                |                                                                                                          |         |
|-------------|----------|------|----------|---------------------------------------|------------------------------|------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------|---------|
| mat'l. code |          |      |          | surface 58 / ISO 1302                 | tolerance ISO 406 / ISO 1101 | projection  | product family 58RF                                                                                      | CODE JP |
| ltr         | ecn no   | dr   | date     | tolerances unless otherwise specified |                              |             | title<br>CAT. NO. TABLE FOR PLASTIC TAPE PACKAGED 1mm SPACING SMT CONNECTOR (Cat. No. SFW__R-1/2STE1 LF) |         |
| AA          | J05-0055 | H.T  | 05-02-04 | angles                                | linear                       |                                                                                                |                                                                                                          |         |
| AB          | J06-0398 | H.T  | 06-09-26 |                                       |                              | scale       | dwg no JSA 95857 sheet 1 of 1 size A4                                                                    |         |
| AC          | S08-0276 | DGOH | 08-08-22 |                                       |                              |                                                                                                |                                                                                                          |         |
|             |          |      |          | dr                                    | H. TAKAKURA                  | 06-09-26                                                                                       | type Product Customer Drawing                                                                            |         |
|             |          |      |          | enr                                   | H. TAKAKURA                  | 06-09-26                                                                                       |                                                                                                          |         |
|             |          |      |          | chr                                   | DENNIS GOH                   | 08-08-22                                                                                       |                                                                                                          |         |
|             |          |      |          | appd                                  | JOEY NG                      | 08-08-22                                                                                       |                                                                                                          |         |
| sheet index | revision | AC   |          |                                       |                              |                                                                                                |                                                                                                          | Rev. AC |

SC\_SFW10 JSA95854 95858 95859  
form: A4



FCIconnect.com




| PT. NO. | PARTS NAME            | CAT. NO.       | MATERIAL          | Q'TY  | NOTE               |
|---------|-----------------------|----------------|-------------------|-------|--------------------|
| 1       | REEL                  | _____          | CARDBOARD         | 1     | COLOR:WHITE/GREY   |
| 2       | PLASTIC (EMBOSS) TAPE | _____          | PET               | _____ | COLOR:TRANSPARENCY |
| 3       | COVER                 | _____          | POLYESTER         | _____ | COLOR:TRANSPARENCY |
| 4       | CONNECTOR             | SFW__R-1ST__LF | SEE ATTACHED DWG. | 2000  | LOWER CONTACT TYPE |

#### NOTES

- THIS IS PLASTIC TAPE PACKAGED CONNECTOR USED FOR FPC/FFC AND COPEES WITH AUTOMATIC MOUNTING (SMT).
- SEE JIS C 0806 (PACKING OF ELECTRONIC COMPONENTS ON CONTINUOUS TAPES (SURFACE MOUNTING DEVICES)) FOR SHAPE AND DIMENSIONS OF PLASTIC (EMBOSS) TAPE AND REEL.
- E DIMENSION IS PORTION OF THE CORE.
- A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

|             |          |      |          |                                       |                            |            |                                                                                           |         |
|-------------|----------|------|----------|---------------------------------------|----------------------------|------------|-------------------------------------------------------------------------------------------|---------|
| mat'l. code |          |      |          | surface 58/ISO 1302                   | tolerance ISO 406 ISO 1101 | projection | product family 58RF                                                                       | CODE JP |
| ltr         | ecn no   | dr   | date     | tolerances unless otherwise specified |                            |            | title<br>PLASTIC TAPE PACKAGED<br>1mm SPACING SMT CONNECTOR<br>(Cat. No. SFW__R-1STE1 LF) |         |
| AA          | J05-0055 | H.T  | 05/02/04 | angles                                | linear ±5                  |            |                                                                                           |         |
| AB          | J06-0398 | H.T  | 06/09/26 | ±5°                                   |                            | scale      | dwg no sheet 1 of 1 size                                                                  |         |
| AC          | S08-0276 | DGOH | 08-08-22 |                                       |                            |            |                                                                                           |         |
|             |          |      |          | dr                                    | H. TAKAKURA                | 06-09-26   | JSA 95858                                                                                 |         |
|             |          |      |          | enr                                   | H. TAKAKURA                | 06-09-26   |                                                                                           |         |
|             |          |      |          | chr                                   | DENNIS GOH                 | 08-08-22   | type Product Customer Drawing                                                             |         |
|             |          |      |          | appd                                  | JOEY NG                    | 08-08-22   |                                                                                           |         |
| sheet index | revision | AC   |          |                                       |                            |            | Rev. AC                                                                                   |         |
|             | sheet    | 1    |          |                                       |                            |            |                                                                                           |         |


SC\_SFW10 JSA95857  
form: A4



| PT. NO. | PARTS NAME            | CAT. NO.       | MATERIAL          | Q'TY  | NOTE               |
|---------|-----------------------|----------------|-------------------|-------|--------------------|
| 1       | REEL                  | _____          | CARDBOARD         | 1     | COLOR:WHITE/GREY   |
| 2       | PLASTIC (EMBOSS) TAPE | _____          | PET               | _____ | COLOR:TRANSPARENCY |
| 3       | COVER                 | _____          | POLYESTER         | _____ | COLOR:TRANSPARENCY |
| 4       | CONNECTOR             | SFW__R-2ST__LF | SEE ATTACHED DWG. | 2000  | UPPER CONTACT TYPE |

NOTES

1. THIS IS PLASTIC TAPE PACKAGED CONNECTOR USED FOR FPC/FFC AND CYPES WITH AUTOMATIC MOUNTING (SMT).
2. SEE JIS C 0806 (PACKING OF ELECTRONIC COMPONENTS ON CONTINUOUS TAPES (SURFACE MOUNTING DEVICES)) FOR SHAPE AND DIMENSIONS OF PLASTIC (EMBOSS) TAPE AND REEL.
3. E DIMENSION IS PORTION OF THE CORE.
4. A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

|             |          |      |          |                                                      |                                                                                     |                                                                                           |              |
|-------------|----------|------|----------|------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------|--------------|
| mat'l. code |          |      |          | surface 58 / tolerance ISO 1302 / ISO 406 / ISO 1101 | projection                                                                          | product family 58RF                                                                       | CODE JP      |
| ltr         | ecn no   | dr   | date     | tolerances unless otherwise specified                |  | title<br>PLASTIC TAPE PACKAGED<br>1mm SPACING SMT CONNECTOR<br>(Cat. No. SFW__R-2STE1 LF) |              |
| AA          | J05-0055 | H.T  | 05-02-04 | angles linear ±5                                     | mm                                                                                  |                                                                                           |              |
| AB          | J06-0398 | H.T  | 06-09-26 | ±5°                                                  | scale                                                                               |                                                                                           |              |
| AC          | S08-0276 | DGOH | 08-08-22 | dr H. TAKAKURA 06-09-26                              |  | dwg no                                                                                    | sheet 1 of 1 |
|             |          |      |          | engr H. TAKAKURA 06-09-26                            |                                                                                     | JSA 95859                                                                                 | size A4      |
|             |          |      |          | chr DENNIS GOH 08-08-22                              |                                                                                     | type Product Customer Drawing                                                             |              |
|             |          |      |          | appd JOEY NG 08-08-22                                |                                                                                     |                                                                                           |              |
| sheet index | revision | AC   |          |                                                      |                                                                                     |                                                                                           | Rev. AC      |

SC\_SFW10 JSA95857  
form: A4

## RECOMMENDED CABLE (FPC)


n : NO. OF CONDUCTOR



| PT. NO. | PARTS NAME      | MATERIAL                             | THICKNESS (μm) |
|---------|-----------------|--------------------------------------|----------------|
| 1       | BASE FILM       | POLYIMIDE OR POLYESTER OR EQUAL      | 25             |
| 2       | CONDUCTOR       | COPPER FOIL(PLATING:SOLDER 1μm MIN.) | 35             |
| 3       | OVERLAY         | POLYIMIDE OR POLYESTER OR EQUAL      | —              |
| 4       | SUPPORTING TAPE | POLYESTER OR POLYIMIDE OR EQUAL      | 188            |

## NOTES

1. NO BURR AT EACH PORTION.
2. NO PEELING IN COMMON USE.
3. TOTAL THICKNESS LIMIT OF EACH MATERIAL (INCLUDING ADHESIVE AGENT) IS SPECIFIED.
4. A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

|             |          |                |          |                                       |             |                            |          |                                                                                     |                                                                                     |                                              |           |         |                          |      |
|-------------|----------|----------------|----------|---------------------------------------|-------------|----------------------------|----------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|----------------------------------------------|-----------|---------|--------------------------|------|
| mat'l. code |          |                |          | surface 58/ISO 1302                   |             | tolerance ISO 406 ISO 1101 |          | projection                                                                          |                                                                                     | product family 58RF                          |           | CODE JP |                          |      |
| ltr         | ecn no   | dr             | date     | tolerances unless otherwise specified |             |                            |          |  |                                                                                     | title                                        |           |         |                          |      |
| AA          | J05-0055 | H.T            | 05-02-04 | angles linear                         |             |                            |          | mm                                                                                  |                                                                                     | RECOMMENDED CABLE<br>(Cat. No. SFW__R-1/2__) |           |         |                          |      |
| AB          | J06-0398 | H.T            | 06-09-26 |                                       |             |                            |          | scale                                                                               |                                                                                     |                                              |           |         |                          |      |
| AC          | S08-0276 | DGOH           | 08-08-22 |                                       |             |                            |          |  |                                                                                     |                                              |           |         |                          |      |
|             |          |                |          | dr                                    | H. TAKAKURA |                            | 06-09-26 |                                                                                     |  |                                              | dwg no    |         | sheet 1 of 1             | size |
|             |          |                |          | enr                                   | H. TAKAKURA |                            | 06-09-26 |                                                                                     |                                                                                     |                                              | JSA 91605 |         | A4                       |      |
|             |          |                |          | chr                                   | DENNIS GOH  |                            | 08-08-22 |                                                                                     |                                                                                     |                                              | type      |         | Product Customer Drawing |      |
|             |          |                |          | appd                                  | JOEY NG     |                            | 08-08-22 |                                                                                     |                                                                                     |                                              |           |         |                          |      |
| sheet index |          | revision sheet |          | AC                                    |             |                            |          |                                                                                     |                                                                                     |                                              |           |         | Rev. AC                  |      |

## RECOMMENDED CABLE (FFC)



n : NO. OF CONDUCTOR



| PT. NO. | PARTS NAME      | MATERIAL                           | NOTE                              |
|---------|-----------------|------------------------------------|-----------------------------------|
| 1       | INSULATOR       | FLAME RESISTING POLYESTER OR EQUAL | _____                             |
| 2       | CONDUCTOR       | COPPER FOIL                        | PLATING:TIN OR SOLDER<br>1um MIN. |
| 3       | SUPPORTING TAPE | FLAME RESISTING POLYESTER OR EQUAL | _____                             |

## NOTES

1. NO BURR AT EACH PORTION.
2. NO PEELING IN COMMON USE.
3. A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

|             |                |      |          |                                       |                            |                                                                                                |                                                       |         |
|-------------|----------------|------|----------|---------------------------------------|----------------------------|------------------------------------------------------------------------------------------------|-------------------------------------------------------|---------|
| mat'l. code |                |      |          | surface 58/ISO 1302                   | tolerance ISO 406 ISO 1101 | projection  | product family 58RF                                   | CODE JP |
| ltr         | ecn no         | dr   | date     | tolerances unless otherwise specified |                            |             | title<br>RECOMMENDED CABLE<br>(Cat. No. SFW__R-1/2__) |         |
| AA          | J05-0055       | H.T  | 05-02-04 | angles                                | linear                     |                                                                                                |                                                       |         |
| AB          | J06-0398       | H.T  | 06-09-26 |                                       |                            | mm                                                                                             | dwg no sheet 1 of 1 size                              |         |
| AC          | S08-0276       | DGOH | 08-08-22 |                                       |                            | scale       |                                                       |         |
|             |                |      |          | dr                                    | H. TAKAKURA                | 06-09-26                                                                                       | JSA 91604                                             |         |
|             |                |      |          | enr                                   | H. TAKAKURA                | 06-09-26                                                                                       |                                                       |         |
|             |                |      |          | chr                                   | DENNIS GOH                 | 08-08-22                                                                                       | type Product Customer Drawing                         |         |
|             |                |      |          | appd                                  | JOEY NG                    | 08-08-22                                                                                       |                                                       |         |
| sheet index | revision sheet | AC   | 1        |                                       |                            |                                                                                                |                                                       | Rev. AC |