LOCKING CIRCUIT BOARD SUPPORTS

Buy One or Buy Bulk&SAVE

BHDF
Metric Double Blind Hole Mount Circuit Board Support

Richco



New



Top Hole:
Press-fit: 7.92mm
Panel Thickness:
6.4mm Min.

Bottom Hole:
Press-fit: 7.92mm
Panel Thickness:
6.4mm Min.

- Fir-tree mount is flexible and will lock into round, threaded, punched or drilled blind holes
- Material: UL94 V-2 Nylon 6/6
- Color: Natural

Item No.	"A" Standoff Height mm	Bulk Pack Qty.
BHDF-3M-01	3	1000
BHDF-4M-01	4	1000
BHDF-6M-01	6	1000
BHDF-8M-01	8	1000
BHDF-10M-01	10	1000
BHDF-12M-01	12	1000
BHDF-14M-01	14	1000
BHDF-16M-01	16	1000
BHDF-18M-01	18	1000
BHDF-20M-01	20	1000

DLCBSHD
Metric Dual Locking Circuit Board Support Heavy Duty

Richco



New



Top Hole:
Snap-lock: 6.3mm
Panel Thickness:
0.8 - 2.2mm

Bottom Hole:
Snap-lock: 6.3mm
Panel Thickness:
0.8 - 2.2mm

- Larger design provides a strong, sturdy mounting method for heavily loaded PCBs
- Easily installed by hand
- Material: Nylon 6/6
- Color: Natural

Item No. Material: UL94 V-2	Item No. Material: UL94 V-0	"A" Standoff Height mm	Bulk Pack Qty.
DLCBSHD-10M-01	DLCBSHD-10M-19	10	1000
DLCBSHD-20M-01	DLCBSHD-20M-19	20	1000
DLCBSHD-25M-01	DLCBSHD-25M-19	25	1000
DLCBSHD-30M-01	DLCBSHD-30M-19	30	1000
DLCBSHD-35M-01	DLCBSHD-35M-19	35	1000

DLCBS2
Dual Locking Circuit Board Support

Richco





Top Hole:
Snap-lock: .187 (4.75)
Panel Thickness:
.031 - .078 (0.79 - 1.98)

Bottom Hole:
Snap-lock: .187 (4.75)
Panel Thickness:
.031 - .078 (0.79 - 1.98)

- Both ends lock by hand, no tools required
- Wings provide a tight fit to the boards and allow for various panel thicknesses
- Nylon 6/6
- Color: Natural

Item No. Material: UL94 V-2	Item No. Material: UL94 V-0	"A" Standoff Height	Bulk Pack Qty.
DLCBS2-3-01	DLCBS2-3-19	3/16 (4.8)	1000
DLCBS2-4-01	DLCBS2-4-19	1/4 (6.4)	1000
DLCBS2-6-01	DLCBS2-6-19	3/8 (9.5)	1000
DLCBS2-8-01	DLCBS2-8-19	1/2 (12.7)	1000
DLCBS2-9-01	DLCBS2-9-19	9/16 (14.3)	1000
DLCBS2-10-01	DLCBS2-10-19	5/8 (15.9)	1000
DLCBS2-12-01	DLCBS2-12-19	3/4 (19.1)	1000
DLCBS2-14-01	DLCBS2-14-19	7/8 (22.2)	1000

DLCBSRA3
Double Locking Support

Richco



Top Hole:
Snap-lock:
.187 (4.8)
Panel Thickness:
.031 - .078 (0.8 - 2.0)

Bottom Hole:
Snap-lock: .187 (4.8)
Panel Thickness:
.031 - .078 (0.8 - 2.0)

Specifications:
- Material: Nylon 6/6
- Color: Natural
- Flame Class: UL94 V-2

Item No.	A In	A mm	Bulk Pack Qty.
DLCBSRA3-6-01	0.188	4.8	1000
DLCBSRA3-8-01	0.500	12.7	1000
DLCBSRA3-10-01	0.625	15.9	1000
DLCBSRA3-12-01	0.750	19.1	1000
DLCBSRA3-14-01	0.875	22.2	1000

SP2
Support Post

Richco



Snap-Lock:
.187 (4.8)
Panel Thickness:
.062 (1.6)

Snap-Lock:
.187 (4.8)
Panel Thickness:
.062 (1.6)

Specifications:
- Material: Nylon 6/6
- Color: Natural
- Flame Class: UL94 V-2

Item No.	A In	A mm	Bulk Pack Qty.
SP2-3-01	0.188	4.8	1000
SP2-4-01	0.250	6.4	1000
SP2-6-01	0.375	9.5	1000
SP2-8-01	0.500	12.7	1000
SP2-10-01	0.625	15.9	1000
SP2-12-01	0.750	19.1	1000
SP2-14-01	0.875	22.2	1000
SP2-16-01	1.000	25.4	1000

Pages 0660 - 0671.indd 662 11/6/2013 4:16:27 PM