

(2,00 mm) .0787"

MMT-XV SERIES

SMT TERMINAL STRIPS

Mates with:
SSM, MMS, TCSD

Features:

- Single or double row
- Vertical or horizontal pin orientation. (See Full Line Catalog for horizontal specifications.)
- Alignment pins
- Locking clips
- Pick & Place Pads
- Polarization option
- Molded with high temperature Liquid Crystal Polymer for infrared or vapor phase reflow soldering.
- Mates with Samtec surface mount sockets, or with other Samtec high temperature through-hole sockets for mixed technology applications.

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com/MMT

Insulator Material:

Black Liquid Crystal Polymer

Flammability Rating:

UL 94V-0

Insulation Resistance:

5000 MΩ min

Operating Temp Range:

-55°C to +105°C with Tin;

-55°C to +125°C with Gold

Dielectric Withstanding Voltage:

600 VAC

Terminal Material:

Phosphor Bronze

Plating:

Au, PdNi or Sn over

50μ" (1,27 μm) Ni

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:






Yes, with Matte Sn plating

Lead Coplanarity:

.006" (0,15 mm) max

Note:

Some lengths, styles and options are non-standard, non-returnable.



ALSO AVAILABLE (MOQ Required)

- Alignment pins
 - Locking clips
- Contact Samtec.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685