



LOC	DIST	REVISIONS 變更				
		P	LTR	DESCRIPTION	DATE	DWN APVD
J			B	RELEASED ECO-12-012349	12MAR13	BL AC




- △ MATERIAL
(1) HOUSING: LCP(UL94V-0, BLACK)
(2) CONTACTS: PHOSPHOR BRONZE
FINISH: CONTACT AREA: Au PL. OVER 1μm MIN. Ni PL..
SOLDERING AREA: 1um MIN TIN OVER 1um MIN. Ni PL..
(3) G-CONT. WITH RETENTION-LEG: BRASS
FINISH: 1um MIN TIN PL. OVER 1um MIN. Ni PL..
△ INDICATE DATE CODE.

OBSOLETE	0.76um MIN.	5-5917593-9
	0.2um MIN.	5917593-9
	CONT.AREA Au PL. THK.	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN WENKE HE 9MAR05	TE Connectivity			
DIMENSIONS: 單位： 耗 mm		CHK STEVEN YAO 9MAR05				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD I.ENOMOTO 9MAR05	NAME 名稱 PLUG ASSY SMT TYPE CHAMP.050 I, BLINDMATE, WITH G-CONT.			
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 製品規格	SIZE A3			
MATERIAL 材料		APPLICATION SPEC 取付適用規格	CAGE CODE 00779			
FINISH 仕上		WEIGHT	DRAWING NO C-5917593			
GENERAL TOLERANCE 10 ≥*: ±0.2 30 ≥*>10: ±0.25 100 ≥*>30: ±0.3 ANGLES: ±3°		CUSTOMER DRAWING		SCALE 尺度 NTS	SHEET 1 OF 2	REV B

LOC J	DIST /	REVISIONS 變更					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位： 耗
mm

GENERAL TOLERANCE
10 ≥*:±0.2
30 ≥*>10:±0.25
100 ≥*>30:±0.3
ANGLES:±3°

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

FINISH
仕上
SEE SHEET 1

MATERIAL
材料
SEE SHEET 1

DWN
CHK
APVD
PRODUCT SPEC
製品規格
APPLICATION SPEC
取付適用規格
WEIGHT

NAME
名称
PLUG ASSY SMT TYPE
CHAMP.050 I, BLINDMATE, WITH G-CONT.

SIZE
A3

CAGE CODE
00779

DRAWING NO
番号
C-5917593

RESTRICTED TO

CUSTOMER DRAWING

SCALE
尺度
NTS

SHEET
2 OF 2

REV
B

TE Connectivity

TE

1470-19 (3/11)