Product Details for 7024AI

7024AI

Tyco Part Number: 1423165-5

Active

Time Delay Relays

Not ELV or RoHS Compliant

Product Highlights:

- 7000 Electropneumatic Timing Series
- Time Delay Relay
- Input Voltage = 120 VAC
- Input Voltage = 110 VAC
- Contact Arrangement = 4 Form C, 4PDT, 4 C/O

View all Features

Quick Links

Check Pricing & Availability
Search for Tooling
Product Feature Selector
Contact Us
About This Product

Documentation & Additional Information

Product Drawings:
- None Available

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- 7000 Series 4 - Pole Timing Relay (PDF, English)

CAD Files:
- None Available

List all Documents

Additional Information:
- Product Line Information

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Product Type = Time Delay Relay
- Termination Type = Screw Terminal

Electrical Characteristics:
- Input Voltage (VAC) = 110, 120
- Contact Rating = 10A @ 240 VAC

Body Related Features:
- Series = 7000 Electropneumatic Timing

Contact Related Features:
- Mounting Options = Panel Mount
- Mode of Operation = Off-Delay
- Delay Time = 6 minutes to 60 minutes
- Type of Control = Knob
- Repeatability, Max. = ± 10%
- Approved Standards = CE Approved, CSA Certified, FM Approved, UL Listed
- Approx. Dimensions (L x W x H) (mm [in]) = 114.80 x 65.30 x 71.90 [4.523 x 2.572 x 2.832]

Configuration Related Features:
- Contact Arrangement = 4 Form C, 4PDT, 4 C/O
- Multiple Timing Ranges = Without

Industry Standards:
- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not relevant for lead free process

Conditions for Usage:
- Temperature Range (°C) = -30 – +75

Other:
- Brand = Agastat

© 2006 Tyco Electronics Corporation All Rights Reserved